



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	Yes

Complementary

Switch function	3-pole
Poles description	3P
Actuator	Key
Control type	Rotary knob
Number of poles	3
Device mounting	Surface
Fixing mode	By screws
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	10 A
Breaking capacity	10 kA
Motor M-rating AS3133	M200 at 500 V
Rotary handle padlocking	2 padlocks 8 mm
Marking	ON-OFF
Marking location	Marking on surface
Height	107 mm
Width	101 mm
Depth	112 mm
Net weight	0.65 kg
Targeted country	Australia


Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	612 g
Package 1 Height	112.5 mm
Package 1 width	112.5 mm
Package 1 Length	106.5 mm
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Weight	7.8 kg
Package 2 Height	250 mm
Package 2 width	214 mm
Package 2 Length	338 mm
Unit Type of Package 3	PAL
Number of Units in Package 3	768
Package 3 Weight	499.2 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile