

# PRODUCT NUMBER: 2318767 **VERTIGO GREY PU 3**

Handling sharp parts in a dry or greasy environment.

## Honeywell

## **Overview**

## **Reference Number**

2318767

## **Product Type**

Gloves

#### Range

Cut and Puncture Protection

#### I ine

Cut resistant

## **Brand**

Honeywell

## Brand formerly known as

**SPERIAN** 

## Industry

- Automotive and Part Manufacturer
   Aviation
   Building and Construction
   Catering
- Energy or Electricity Glass Industries Logistics Maintenance Metal steel Paper Industries
- Services Telecoms Transportation Utilities

#### **Product Use**

Handling sharp parts in a dry or greasy environment.

## **Features & Benefits**

## **Feature**

White Spectra®/lycra® knitted glove Grey polyurethane coating on palm and tips of fingers

## Elastic wrist Benefit

COMFORT

The knitting technique helps to obtain a glove that conforms snugly to the hand, with good dexterity.

The glove offers maximum comfort and added sturdiness.

The cool Spectra® touch gives an added sensation of comfort.

The tight knit (gauge 13) gives the glove perfect support, limits the penetration of dirt and offers a good touch.

The glove's ventilated back optimises its breathability.

RESISTANCE

## **VERTIGO GREY PU 3 - 2318767**

The Spectra®/lycra® thread provides outstanding properties against cuts.

The polyurethane coating at the palm and fingertips provides outstanding abrasion resistance.

Caution! Do not expose this glove to the heat.

### **HYGIENE**

Its white colour enhances the glove's hygiene and cleanliness.

Its grey coating enables work in a slightly soiled environment.

## **Technical Description**

## Description

CE CATEGORY: II Intermediary risks In accordance with standards: EN 420-2003 EEC Basic standards EN 388-2003 Mechanical hazards

### CHARACTERISTICS:

White Spectra®/lycra® knitted glove Grey polyurethane coating on the palm and fingertips Elastic wrist

## **Product Technology**

Knitted Coated

## Gauge

12

### Glove/liner color

White and grey

## **Coating Type**

Spectra® and lycra®

## Length

23,5 cm

## Harmlessness

In conformity with the European standards

## Dexterity

Class 5

## Sizes

6 to 11

## EN 388 - Mechanical Hazards Abrasion Resistance

Abrasion resistance	4
Cutting resistance	3
Tear resistance	4
Puncture resistance	2

## **Packaging Label**

## **Tagging**

CE HONEYWELL 2318767 XX EN 420 EN 388 : 4342

## **Certifications**

E.C. Declaration of Conformity

## **EC Category PPE**

2

## **Quality Assurance**

ISO 9001 / 2000



## **Additional Information**

**User Manual** 

UI 102

**User Information Sheet** 

102

## **Maintenance**

## **Storage Information**

Minimum packaging 10 pairs. Cartons of 100 pairs.

## **Care Instructions**

This article can be cleaned. For cleaning instructions, please contact Honeywell Safety Products.

© Honeywell International Inc.



In application of the Directive ref. 89/686/EEC of the 21<sup>st</sup> of December 1989, concerning the alignment of member state legislation relating to personal protective equipment and the decrees n° 92-765, 766 and 768 of 29<sup>th</sup> of July 1992 concerning the transposition of this Directive into French law,

## CTC

4,rue Hermann Frenkel - 69367 Cedex 07 - France
Tel +33 (0)4 72 76 10 10 - Fax +33 (0)4 72 72 76 10 00 - E-Mail : ctclyon@ctcgroupe.com - www.ctc.fr

authorized by decrees of the Ministry of Work, Employment and Health of the 20<sup>th</sup> of December 2010, registered under the number 0075, published in OJEC, delivers:

# EC-TYPE EXAMINATION CERTIFICATE 0075/797/162/02/16/0131

To the following model of personal protective equipment #

\* reference of the model:

23 187 67

\* protective glove against

mechanical risks...

\* Manufacturer :

## HONEYWELL SAFETY PRODUCTS EUROPE

Immeuble Edison ZI-Paris Nord II 33, Rue des Vanesses 95 958 ROISSY France

Description of the protective glove, reference of technical rules verified in the context of the CE type examination and informations indicated on the product are detailed in the following pages of this certificate.

Issued by Lionel GAUDILLERE

Drawn up in Lyon, on February 02nd, 2016 Update 01 of June 16th, 2016



NOTA: Any modification to new items of the personal protective equipment object of this CE type approval certificate or any modification of the information contained in the manufacturer technical file which served for the deliverance of the CE type approval certificate (change of adress, change of company status) should be brought to the attention of the notified body in accordance with law n° R. 4313-38 of the French Code of Work.



# 1. DESCRIPTION OF THE PROTECTIVE GLOVE

According to the technical file index : 02

Reference: 23 187 67

Basic Model

Dated: JUNE 2016

Knitted glove with Polyethylene high tenacity / lycra yarns.PU coating in grey color, on the palm and fingertips. Blue elastic wrist 60mm + overlock:T06-green, T07-red, T08-blue, T09-yellow, T10-white, T11 orange

## Available sizes:

06 07 08 09 10 11

## Visual description:



## Material:

	Color	Material	Gauges	Thickness
PALM	Natural	Polyethylene high tenacity/lycra	13	
	Grey	PU		1,1mm
BACK	Natural	Polyethylene high tenacity/lycra 13		
CUFF	Natural	Polyethylene high tenacity/lycra	13	
	Blue	elastic rubber	13	
BINDING	green/red/blue/yello w/white/orange	PES		



## 2. PROTECTION SCOPE

Compliance with the essential requirements of the Directive 89/686/EEC has been verified by using following technical rules:

- \* EN 420:2003+A1:2009
- General requirements for gloves and test methods

\* EN 388:2003

- Protective glove against mechanical risks
- \* At the date of certificate the product is in compliance with Annex XVII of REACh regulation (n° 1907/2006 and revisions)
- \* This product is a category II.

# References of test reports performed in order to verify the compliance with the requirements of the technical rules :

Laboratory	СТС	Other
EN 420	L151016615_1 L151016616_1 L151219369_1	
Azo	L150609368-1 L151016616_1	
EN 388	L151016615_1 L160100138_1	S151210954_3
OTHER	L151016616_1 L1510_16589 L160508559_1	

# Performance levels offered against mechanical risks (EN 388:2003) are:

Abrasion resistance	Blade cut resistance	Tear strength resistance	Puncture resistance
4	3	4	2

The levels of performance have been measured on the palm




## 3. MARKING

# Each glove is clearly marked with the following information:

- \* Logo of the authorized representative:
- \* **(€** marking
- \* reference of the model: 23 187 67
- \* size
- \* pictogram for mechanical risks followed by the performance levels
- \* information pictogram

## Marking example:





# **E.C.** Declaration of Conformity

The manufacturer or its legal representative supplier in the European Community:

Honeywell Safety Products Europe

<u>Declares that the Personal Protective Equipment described here after conforms to the provisions of the European Council Directive 89/686/CEE:</u>

Designation: VERTIGO GREY PU 3

Reference: 2318767

Standard(s): EN 388, EN 420

This PPE is the object of the below EC examination certificate n°:

## **Delivered by:**

CENTRE TECHNIQUE DU CUIR 4 rue Hermann Frenkel 69367 Lyon Cedex 07

Drawn up in Lyon, on the 24/05/2017

By: Fabrice beaugeard

**Division**: Gloves

HONEYWELL SAARTY PRODUCTS EUROPE Immeuble Edison - 21 Pais, Nord II - 33 ne des Vanaueses BP 55288 Villepinte - 5038 FOLSEY - 756 CEDEX SAS au capater 17 55 000 - 2019 - 2019 - 2019 7 00197 Tel - 4331 4996 7979 - 2019 - 331 4990 7980

> ZI Paris Nord II 33, rue des Vanesses BP 50288 95958 Roissy CDG France Tel: +33 (0) 49 90 79 79 Fax: +33 (0)1 49 90 79 80

www.honeywellsafety.com