

Neodymium Ring Magnet

FEATURES

- Neodymium Magnets For Science, Innovation, Engineering And Industry
- Rare Earth Magnets One Of The strongest Type of Permanent Magnet Currently Made
- Maximum Working Temperature is 176 F (80 C)
- Ni+Cu+Ni Triple Layer Coated (Salt Spray Test 24 Hours)
- N35 Grade
- Magnetization Direction: Axially Magnetized
- Tolerance :±0.05mm

RS PRO Neodymium Ring Magnet

RS Stock No.:

2192226

2192254

2192227

2192255

2192249

2192256



Product Description

RS brand provides strong high-quality neodymium-iron-boron (NdFeB) magnets. Neodymium magnets for science, innovation, engineering, and industry. This is made with the world's most advanced magnetic materials.

Rare earth magnets are the strongest type of permanent magnet currently made. They are amazingly powerful for their size and have innumerable uses. They are magnetized through the thickness. They are composed of neodymium iron boron magnetic material and are plated

Neodymium Ring Magnet

in nickel-copper-nickel for a shiny corrosion-resistant finish. The maximum working temperature is 176 F (80 C).

Every magnet has a triple coating of nickel, copper, and nickel again to prevent corrosion. Our Neodymium magnets are also commonly used in engineering and manufacturing where compact size and maximum strength are required. They also have many uses in creative applications such as models and theatre design, furniture making, exhibition stands, and packaging.

Similar Products

Stock No.	Brand	Product Name	OD (mm)	ID (mm)	Thickness (mm)	Coating	Magnetization Direction	Unit/ Tube
2192226	RS PRO	Neodymium Magnet, Ring Shape (Counter Sunk Hole), OD20mm, ID6mm, Thickness 5mm, S-N Pole	20	6	5	NiCuNi	Same With Thickness	5
2192227	RS PRO	Neodymium Magnet, Ring Shape (Counter Sunk Hole), OD20mm, ID6mm, Thickness 5mm, N-S Pole	20	6	5	NiCuNi	Same With Thickness	5
2192249	RS PRO	Neodymium Magnet, Ring Shape (Counter Sunk Hole), OD20mm, ID6.5mm, Thickness 10mm	20	6.5	10	NiCuNi	Same With Thickness	1
2192254	RS PRO	Neodymium Magnet, Ring Shape (Counter Sunk Hole), OD19mm, ID4.5mm, Thickness 7.6mm	19	4.5	7.6	NiCuNi	Same With Thickness	5
2192255	RS PRO	Neodymium Magnet, Ring Shape (Counter Sunk Hole), OD17.5mm, ID4.5mm, Thickness 4mm	17.5	4.5	4	NiCuNi	Same With Thickness	5
2192256	RS PRO	Neodymium Magnet, Ring Shape (Counter Sunk Hole), OD15.4mm, ID3.5mm, Thickness 3.25mm	15.4	3.5	3.25	NiCuNi	Same With Thickness	5