



### Shrinkable markers "Continuous Tube", thermal transfer

#### TLFX - 2:1 Rail LFH

TLFX is a rail approved 2:1 heatshrink material supplied as a continuous tube and printable on both sides. The supplied accessories allow users to either perforate the tubing at pre-determined lengths (P4000), or fully sever the markers (S4000) whilst printing with the TrakMark DS or TT4000+ printer. Print with HellermannTyton's premium range of thermal printers and ribbons.

Printers: TrakMark DS, TT4000+ and TT430

Ribbons: TTDTHOUT, TTRC+

Accessories for TrakMark DS and TT4000+: Perforator (P4000), Cutter (S4000)

Accessories for TT430: Cutter (S430), Perforator (P430)

Software: TagPrint Pro

#### Features and Benefits

- Shrink ratio 2:1
- Available in yellow, white on request
- Cable range 50.8 mm to 1.2 mm
- Halogen Free
- Low smoke propagation, density and toxicity
- High Oxygen Index value (38 %)
- Meets EN45545-2 (HL3, HL2, HL1)
- Delivery in convenient storage boxes
- Easy label design with TagPrint Pro



TLFX.

<b>MATERIAL</b>	Polyolefin, cross-linked (PO-X)
<b>Operating Temperature</b>	-55 °C to +105 °C
<b>Minimum Shrink Temperature</b>	+100 °C
<b>Shrink Ratio</b>	2:1
<b>Recommended Ribbon Type</b>	TTDTHOUT
<b>Specifications</b>	BS-6853:1999, BS-EN ISO 4589-2, DIN 53438-3: 1984, DIN 5510-2, EN 45545-2: 2013 (R22 & R23, HL1, HL2, HL3), EN ISO 11925-2: 2002, NF F 16-101, NF X 70-100-1: 2006, NF X 70-100-2: 2006, UNI CEI 11170-3

RoHS ✓

HF ✓

LFH ✓




TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Pack Cont.	Colour	Article-No.
TLFX24WH	2.4	1.2	0.57	144 m	White (WH)	554-51000
TLFX24YE	2.4	1.2	0.57	144 m	Yellow (YE)	554-51001
TLFX32WH	3.2	1.6	0.58	126 m	White (WH)	554-51100
TLFX32YE	3.2	1.6	0.58	126 m	Yellow (YE)	554-51101
TLFX48WH	4.8	2.4	0.61	108 m	White (WH)	554-51200
TLFX48YE	4.8	2.4	0.61	108 m	Yellow (YE)	554-51201
TLFX64WH	6.4	3.2	0.61	90 m	White (WH)	554-51300
TLFX64YE	6.4	3.2	0.61	90 m	Yellow (YE)	554-51301

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.



**BS DIN EN NF F UNI CEI**

For product specific approvals and specifications please refer to the Appendix.



### Shrinkable markers "Continuous Tube", thermal transfer

TLFX - 2:1 Rail LFH



TYPE	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Pack Cont.	Colour	Article-No.
TLFX95WH	9.5	4.8	0.66	72 m	White (WH)	554-51400
TLFX95YE	9.5	4.8	0.66	72 m	Yellow (YE)	554-51401
TLFX127WH	12.7	6.4	0.68	54 m	White (WH)	554-51500
TLFX127YE	12.7	6.4	0.68	54 m	Yellow (YE)	554-51501
TLFX190WH	19.0	9.5	0.69	30 m	White (WH)	554-51600
TLFX190YE	19.0	9.5	0.69	30 m	Yellow (YE)	554-51601
TLFX254WH	25.4	12.7	0.69	30 m	White (WH)	554-51700
TLFX254YE	25.4	12.7	0.69	30 m	Yellow (YE)	554-51701
TLFX381WH	38.1	19.0	0.70	13 m	White (WH)	554-51800
TLFX381YE	38.1	19.0	0.70	13 m	Yellow (YE)	554-51801
TLFX508WH	50.8	25.4	0.73	10 m	White (WH)	554-50900
TLFX508YE	50.8	25.4	0.73	10 m	Yellow (YE)	554-50901

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.