

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)

Header, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Color: green, Contact surface: Tin, Mounting: Soldering



The figure shows a 10-position version of the product

### Why buy this product

- ☑ Plug-in direction parallel to the conductor axis
- ✓ W type with stand-off



## **Key Commercial Data**

Packing unit	50 pc
GTIN	4 017918 027759
Weight per Piece (excluding packing)	4.62 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### **Dimensions**

Length	12 mm
Pitch	5.00 mm
Dimension a	45 mm
Constructional height	13 mm
Length of the solder pin	3.5 mm
Pin dimensions	1 x 1 mm
Hole diameter	1.4 mm

#### General

Range of articles	MSTBW 2,5/G



## Technical data

### General

Insulating material group	Illa
Rated surge voltage (III/3)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (II/2)	4 kV
Rated voltage (III/3)	250 V
Rated voltage (III/2)	320 V
Rated voltage (II/2)	400 V
Connection in acc. with standard	EN-VDE
Nominal current I <sub>N</sub>	12 A
Maximum load current	12 A
Insulating material	РВТ
Flammability rating according to UL 94	V0
Color	green
Number of positions	10

## Classifications

## eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

### **ETIM**

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

## **UNSPSC**

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

# Approvals

### Approvals



# Approvals

EAC

Approvals				
CSA / VDE Gutachten mit Fertigungsüberwachung / IECEE CB Scheme / CCA / EAC / cULus Recognized				
Ex Approvals				
Approvals submitted				
Approval details				
CSA 1				
	В		D	
Nominal current IN	15 A		10 A	
Nominal voltage UN	300 V		300 V	
VDE Gutachten mit Fertigungsüberv		12 A	300 V	
		12 A 250 V	300 V	
VDE Gutachten mit Fertigungsüberv Nominal current IN			300 V	
VDE Gutachten mit Fertigungsüberv  Nominal current IN  Nominal voltage UN  IECEE CB Scheme		250 V	300 V	
VDE Gutachten mit Fertigungsüberv  Nominal current IN  Nominal voltage UN  IECEE CB Scheme		250 V	300 V	
VDE Gutachten mit Fertigungsüberv  Nominal current IN  Nominal voltage UN  IECEE CB Scheme		250 V	300 V	
VDE Gutachten mit Fertigungsüberv  Nominal current IN  Nominal voltage UN  IECEE CB Scheme		250 V	300 V	
VDE Gutachten mit Fertigungsüberv  Nominal current IN  Nominal voltage UN  IECEE CB Scheme CB  Nominal current IN  Nominal voltage UN  CCA		250 V 12 A 250 V	300 V	
VDE Gutachten mit Fertigungsüberv  Nominal current IN  Nominal voltage UN  IECEE CB Scheme CB  Nominal current IN  Nominal current IN		250 V	300 V	



# Approvals

cULus Recognized			
	В	D	
Nominal current IN	15 A	10 A	
Nominal voltage UN	300 V	300 V	

#### Accessories

Accessories

Coding element

Coding star - CR-MSTB - 1734401



Coding section, inserted into the recess in the header or the inverted plug, red insulating material

#### Filler plug

Accessories - MSTB-BL - 1755477



Keying cap, for forming sections, plugs onto header pin, green insulating material

#### Labeled terminal marker

Marker card - SK 5/3,8:FORTL.ZAHLEN - 0804183



Marker card, Card, white, labeled, Horizontal: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - (99)100, Mounting type: Adhesive, for terminal block width: 5 mm, Lettering field: 5 x 3.8 mm

### Additional products

Printed-circuit board connector - FKCVW 2,5/10-ST - 1910115



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Push-in spring connection, Color: green, Contact surface: Tin



#### Accessories

Printed-circuit board connector - FKC 2,5/10-ST - 1910432



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Push-in spring connection, Color: green, Contact surface: Tin

Printed-circuit board connector - MSTB 2,5/10-ST - 1754601



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Screw connection, Color: green, Contact surface: Tin

Printed-circuit board connector - MSTBP 2,5/10-ST - 1765852



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Screw connection, Color: green, Contact surface: Tin

Printed-circuit board connector - MVSTBW 2,5/10-ST - 1792605



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Screw connection, Color: green, Contact surface: Tin

Printed-circuit board connector - MVSTBR 2,5/10-ST - 1792090



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Screw connection, Color: green, Contact surface: Tin



#### Accessories

Printed-circuit board connector - MSTBT 2,5/10-ST - 1779916



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Screw connection, Color: green, Contact surface: Tin

Printed-circuit board connector - FRONT-MSTB 2,5/10-ST - 1779495



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Screw connection, Color: green, Contact surface: Tin

Printed-circuit board connector - SMSTB 2,5/10-ST - 1768833



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Screw connection, Color: green, Contact surface: Tin

Printed-circuit board connector - MSTB 2,5/10-STZ - 1759004



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Screw connection, Color: green, Contact surface: Tin

Printed-circuit board connector - FKCVR 2,5/10-ST - 1909799



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Push-in spring connection, Color: green, Contact surface: Tin




### Accessories

Printed-circuit board connector - FKCT 2,5/10-ST - 1909294




Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 10, Pitch: 5 mm, Connection method: Push-in spring connection, Color: green, Contact surface: Tin

# **Drawings**



Type: MSTB 2,5/...-ST with MSTBW 2,5/...-G

### Dimensional drawing



Phoenix Contact 2015 © - all rights reserved http://www.phoenixcontact.com