


ITEM NUMBER	MATERIAL	COLOR
43680-2003	UL94V-0 NYLON	BLACK
43680-1003	UL94V-2 NYLON	NATURAL (TRANSLUCENT)
43680-3003	UL94V-2 NYLON, IEC 60335-1, GLOW WIRE CAPABLE	BLACK

**NOTES:**

1. MATERIAL: SEE CHART.
2. FINISH: NONE.
3. PRODUCT SPECIFICATION: PS-44441-9999.
4. PACKAGING: PK-43680-001.
5. THIS CONNECTOR HOUSING FOR USE WITH 43178-\*\*\*\* TERMINALS.
6. THIS CONNECTOR HOUSING WILL MATE TO 43335-\*\*\*\*, 43179-\*\*\*3 AND 44441-\*\*\*3 HOUSINGS.
7. PARTS CONFORM TO CLASS B REQUIREMENTS OF COSMETIC SPEC PS-45499-002.  
- SOME PARTS MAY HAVE A BLEMISH NEAR THE GATE THAT DOES NOT AFFECT FUNCTIONALITY.

LOCKING NUB IS LOCATED HERE



43680-\*003  
(NO SCALE)

<b>GATE BLEMISH</b> IEC NO: UCP2015-2359 DRWIN: DFOX 2015/01/06 CHKD: BANDERSON 2015/01/06 APPR: FSMITH 2015/01/09	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE <b>IN/MM</b>	SCALE <b>4:1</b>	DESIGN UNITS <b>INCH</b>	THIRD ANGLE PROJECTION															
		<table border="1"> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> <tr> <td>4 PLACES</td> <td>± .010</td> <td>± .004</td> </tr> <tr> <td>3 PLACES</td> <td>± .012</td> <td>± .005</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.25</td> <td>± .014</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.35</td> <td>± .014</td> </tr> <tr> <td>0 PLACE</td> <td>± .010</td> <td>± .004</td> </tr> </table>		mm	INCH	4 PLACES	± .010	± .004	3 PLACES	± .012	± .005	2 PLACES	± 0.25	± .014	1 PLACE	± 0.35	± .014	0 PLACE	± .010	± .004	DRAWN BY CM DATE 03/22/96
	mm	INCH																			
4 PLACES	± .010	± .004																			
3 PLACES	± .012	± .005																			
2 PLACES	± 0.25	± .014																			
1 PLACE	± 0.35	± .014																			
0 PLACE	± .010	± .004																			
MATERIAL NO. <b>SEE CHART</b>		DOCUMENT NO. <b>SD-43680-*003</b>		SHEET NO. <b>1 OF 1</b>																	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																					