

1.06/3

Universal puller

2-arm pattern

Code	ETIM
8000740	EC002110
EAN	UNSPSC
4036976104202	27-11-17-12
Country of origin	eCl@ss
Germany	21-04-15-01
Customs tariff number	
	82055980



Article description

- Proven model for safe and fast removal of discs, wheels, ball bearings etc.
- Strong drop forged pattern
- Scale for uniform adjustment of the puller legs. Allows centred pulling, with optimised application of force, even when extremely high pulling forces are required
- Can be used as external and internal puller by repositioning the legs
- Interchangeable legs available for several clamping depths
- Upgradeable with hydraulic spindle (see table)

Article information

Contents (Qty of pieces)	1	Clamping width (max.) external pulling [mm]	250 mm
Graduation	yes	Spindle thread size	G 3/4 x 280
reversible arms available	no	Total length [mm]	315 mm
Clamping bracket available	no	Total width [mm]	330 mm
Net weight [kg]	7,2 kg	Total height [mm]	65 mm
Hook brake available	no	Clamping width a2 (min.) internal pulling [mm]	125 mm
Hook can be moved parallel	no	Clamping width a2 (max.) internal pulling [mm]	330 mm
Quick release lever available	no	Width of hooked foot [mm]	36 mm
3D data available	no	Usable depth of hooked foot d2 [mm]	28 mm
Spindle anti-slip device	no	Thickness of hooked foot at tip	6.5 mm
Screws included	no	Width across flats [mm]	27 mm
Anti-slip device on the spindle	no	Tractive force (max.) [t]	7.5
Exchangeable spindle tip	no	Hydraulic spindle optional	1.06/HSP2
Can be retrofitted with hydraulic spindle	yes	Number of arms	2
Usable clamping reach [mm]	200 mm	Hydraulic spindle available	no