



CG 17-125

Compact angle grinders, Ø 125 mm

Ergonomic 1700 W compact angle grinder with high power reserve for effective sanding and cutting.

Product number: 7 222 90 60 23 0

Details

- + Thanks to the powerful 1700 watt motor and a significantly smaller handle (195 mm), faster and more convenient work can be undertaken on the construction site and in metal workshops.
- + New cooling concept with ventilation inlets as well as a removable dust protection filter ensures the tool a longer service life even in extreme conditions.
- + Safety features, such as kick-back monitoring, soft start, restart protection, overload protection and anti-vibration handle, ensure extensive user protection.
- + Robust motor for daily use.
- + Long-life thanks to overload protection and long carbon brush service life.
- + Rapid work progress thanks to powerful motor.
- + Gearbox head can be rotated 90° for high versatility.
- + Abrasive materials can be changed at speed and without the need for any tools: quick-clamping nut included in scope of supply as standard.
- + Good ability to cope with overload thanks to direct motor cooling.
- + Cable length 4 m.

Price includes

- + 1 anti-vibration handle
- + 1 clamping nut
- + 1 two-hole spanner
- + 1 adapter flange
- + 1 wheel guard
- + 1 safety hood for cutter

Product feature

- + Soft start
- + Blockage monitoring
- + Electronic speed preselection
- + Restart protection
- + Electronic overload protection
- + Kick-back check

Application

Roughing-down





FEIN

Deburring

+

Dividing

+

Brushing

+

Satin-finishing

++

Polishing

++

+ suitable

++ well suitable

Technical data

TECHNICAL DATA

Input

1,700 W

Output

1,010 W

Speed, no load

11 500 rpm

Grinding disc Ø

125 mm

Elast. Backing pad Ø

125 mm

Flange

M 14

Cable with plug

4 m

Weight according to
EPTA

2.40 kg

VIBRATION AND SOUND EMISSION VALUES

Sound pressure level LpA
Uncertainty of measured value
KpA

96 dB
3 dB

Sound power level LWA
Uncertainty of measured value
KWA

104 dB
3 dB

Sound peak value
LpCpeak
Uncertainty of measured value
KpCpeak

108 dB
3 dB

Vibration value 1 α_{hv} 3-
way
Uncertainty of measured value
K α

5,7 m/s²
1,5 m/s²

Vibration value 2 α_{hv} 3-
way
Uncertainty of measured value
K α

2,4 m/s²
1,5 m/s²

Application examples



FEIN

