



 PRODUCT-DETAILS

B7-40-00-80

B7-40-00-80 Mini Contactor 220 ... 240 V AC - 4 NO - 0 NC - Screw Terminals



General Information

Extended Product Type	B7-40-00-80
Product ID	GJL1311201R8000
EAN	4013614152399
Catalog Description	B7-40-00-80 Mini Contactor 220 ... 240 V AC - 4 NO - 0 NC - Screw Terminals
Long Description	<p>The B7-40-00 mini contactor is a compact 4 pole contactor with screw terminals. They are ideally suited for applications where reliability is a must and space is at a premium.</p> <p>Mini contactors are used in residential buildings, commercial buildings and industrial applications for the control of single or three-phase loads up to 5.5 kW (AC-3) and 20 A (AC-1) or switching of control signals. Further features are the silent coil, a switch position indication and the integrated possibility for rail or wall mounting.</p>

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080

Popular Downloads

EPLAN Data	9AAC201023_EPLAN
Data Sheet, Technical Information	1SBC100214C0202
Instructions and Manuals	2CDC102047M6801
CAD Dimensional Drawing	2CDC001079B0201

Dimensions

Product Net Width	52.5 mm
Product Net Depth / Length	46.7 mm
Product Net Height	57.5 mm
Product Net Weight	0.175 kg
Dimension Diagram	GJL1200436F0001

Technical

Number of Main Contacts NO	4
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	0
Number of Auxiliary Contacts NC	0
Number of Poles	4P
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1 IEC 60335-2-40 A2L
Rated Operational Voltage	Main Circuit 690 V AC Main Circuit 220 V DC
Rated Frequency (f)	Control Circuit 400 Hz Control Circuit 50 Hz Control Circuit 60 Hz Main Circuit 60 Hz Main Circuit 50 Hz Main Circuit DC
Conventional Free-air Thermal Current (I_{th})	Main Circuit 20 A
Rated Operational Current AC-1 (I_e)	(220 / 240 V) 40 °C 20 A (220 / 240 V) 55 °C 16 A (380 / 440 V) 40 °C 20 A (380 / 440 V) 55 °C 16 A (690 V) 40 °C 6 A (690 V) 55 °C 6 A
Rated Operational Current AC-3 (I_e)	(230 V) 55 °C 12 A (400 V) 55 °C 12 A (500 V) 55 °C 9 A (690 V) NO 55 °C 3.5 A
Rated Operational Power AC-3 (P_e)	(230 V) Three Phase 3 kW (400 V) Three Phase 5.5 kW (500 V) Three Phase 5.5 kW (690 V) Three Phase, NO 3 kW
Rated Breaking Capacity AC-3	8 x I_e / AC-3
Rated Making Capacity	10 x I_e / AC-3

AC-3	
Rated Short-time Withstand Current Low Voltage (I_{cw})	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 96 A
Rated Insulation Voltage (U_i)	690 V acc. to UL/CSA 600 V
Rated Impulse Withstand Voltage (U_{imp})	Main Circuit 6 kV
Maximum Electrical Switching Frequency	(AC-1) 300 cycles per hour (AC-3) 600 cycles per hour (DC-1) 600 cycles per hour (DC-3) 600 cycles per hour
Mechanical Durability	Nr. Operations 10000000 cycle
Coil Operating Limits	(acc. to IEC 60947-4-1) for AC supply 0.85 ... 1.1 x U_c (at $\theta \leq 55$ °C)
Rated Control Circuit Voltage (U_c)	220 ... 240 V AC
Coil Consumption	Average Holding Value 50 Hz 3.5 V·A Average Pull-in Value 50 Hz 3.5 V·A
Power Loss	at Rated Operating Conditions AC-1 per Pole 1.4 W
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Connecting Capacity Main Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 mm ² Flexible with Insulated Ferrule 1/2x 1 ... 2.5 mm ² Flexible 1/2x 1 ... 2.5 mm ² Rigid 1/2x 1 ... 4 mm ²
Connecting Capacity Control Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 mm ² Flexible with Insulated Ferrule 1/2x 1 ... 2.5 mm ² Flexible 1/2x 1 ... 2.5 mm ² Rigid 1/2x 1 ... 4 mm ²
Wire Stripping Length	Main Circuit 9 mm
Degree of Protection	Control Circuit Terminals IP20 Main Circuit Terminals IP20
Recommended Screw Driver	M3 Pozidriv 1
Tightening Torque	Control Circuit 0.8 ... 1.1 N·m Main Circuit 0.8 ... 1.1 N·m
Terminal Type	Screw Terminals
Mini Contactor Type	Mini Contactor
Product Name	Mini Contactor

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
General Use Rating UL/CSA	(600 V AC) 16 A
Horsepower Rating UL/CSA	(115 V AC) Single Phase 0.75 Hp (200 V AC) Three Phase 2 Hp (220 ... 240 V AC) Three Phase 3 Hp (230 V AC) Single Phase 1.5 Hp (440 ... 480 V AC) Three Phase 5 Hp (550 ... 600 V AC) Three Phase 5 Hp
Connecting Capacity Main Circuit UL/CSA	Stranded 1/2x 22-10 AWG
Tightening Torque UL/CSA	Control Circuit 7 in·lb Main Circuit 7 in·lb
Full Load Amps Motor Use	(115 V AC) Single Phase 13.8 A (200 V AC) Three Phase 7.8 A (220 ... 240 V AC) Three Phase 9.6 A (230 V AC) Single Phase 10 A (440 ... 480 V AC) Three Phase 7.6 A

(550 ... 600 V AC) Three Phase 6.1 A

Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +80 °C
Maximum Operating Altitude Permissible	2000 m
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 15g
Resistance to Vibrations	5g 5 ... 150 Hz

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202
RoHS Declaration	2CMT2021-006277
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006525
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

ABB EcoSolutions

End Of Life Disassembling Instructions	1SBC100156C0269
Environmental Product Declaration - EPD	1SAC200409H0001

Certificates and Declarations

A2L Certificate – IEC	1SAA938000-4601
BV Certificate	1SAA920000-0204
CB Certificate	1SAA938000-2002
CQC Certificate	CQC2003010304064033
Declaration of Conformity - CCC	2020980304001854
Declaration of Conformity - CE	1SAD101100-3101
Declaration of Conformity - UKCA	1SAD201100-3101
DNV GL Certificate	1SAA938000-0306
EAC Certificate	1SAA920000-2702
KC Certificate	1SAA938000-1501
LR Certificate	1SAA938000-0504
RMRS Certificate	1SAA938000-0704
UL Certificate	E191658-19881208

Container Information

Package Level 1 Units	box 10 piece
Package Level 1 Width	115 mm
Package Level 1 Depth / Length	280 mm
Package Level 1 Height	54 mm
Package Level 1 Gross Weight	1.82 kg
Package Level 1 EAN	4013614417009

External Classifications and Standards

Object Classification Code	Q
ETIM 7	EC000066 - Power contactor, AC switching
ETIM 8	EC000066 - Power contactor, AC switching
ETIM 9	EC000066 - Power contactor, AC switching
eClass	V11.0 : 27371003
UNSPSC	39121529
IDEA Granular Category Code (IGCC)	4761 >> Magnet contactor, AC-switching

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
GJL1201317R0002	CA6-11E Auxiliary Contact 1NO/1NC screw terminal, side mounted	CA6-11E	1	piece
GJL1201317R0003	CA6-11M Auxiliary Contact 1NO/1NC screw terminal, side mounted	CA6-11M	1	piece
GJL1201317R0004	CA6-11N Auxiliary Contact 1NO/1NC screw terminal, side mounted	CA6-11N	1	piece
GJL1201330R0003	CAF6-11M Auxiliary Contact 1NO/1NC screw terminal, front mounted	CAF6-11M	1	piece
GJL1201330R0006	CAF6-20E Auxiliary Contact 2NO/0NC screw terminal, front mounted	CAF6-20E	1	piece
GJL1201330R0011	CAF6-02M Auxiliary Contact 0NO/2NC screw terminal, front mounted	CAF6-02M	1	piece
GJL1201330R0007	CAF6-20M Auxiliary Contact 2NO/0NC screw terminal, front mounted	CAF6-20M	1	piece
GJL1201330R0012	CAF6-02N Auxiliary Contact 0NO/2NC screw terminal, front mounted	CAF6-02N	1	piece
GJL1201330R0008	CAF6-20N Auxiliary Contact 2NO/0NC screw terminal, front mounted	CAF6-20N	1	piece
GJL1201330R0002	CAF6-11E Auxiliary Contact 1NO/1NC screw terminal, front mounted	CAF6-11E	1	piece
GJL1201330R0004	CAF6-11N Auxiliary Contact 1NO/1NC screw terminal, front mounted	CAF6-11N	1	piece
GJL1201330R0010	CAF6-02E Auxiliary Contact 0NO/2NC screw terminal, front mounted	CAF6-02E	1	piece
GJL1201906R0001	LT6-B Mini Contactor Cover Cap	LT6-B	1	piece
GJL1201904R0001	BN6 Plunger for Mini Contactor (50 pcs) BN6 Plunger for Mini Contactor 50 pcs	BN6	1	piece

Categories

Low Voltage Products and Systems → Control Products → Contactors → Mini Contactors

