

# Product data sheet

Specifications



Repacked Data socket, New Unica, mechanism, RJ45, STP, straight, click, shuttered, anthracite

NU341754W



This repacked option saves 0.377 over the standard condition

## Main

|                           |                                   |
|---------------------------|-----------------------------------|
| Range                     | New Unica                         |
| Product or component type | Data socket                       |
| Device application        | Communication                     |
| Device presentation       | Mechanism                         |
| Colour tint               | Anthracite (RAL 7021)             |
| Data socket type          | RJ45 8 contact(s) Cat.6 < 250 MHz |
| Provided equipment        | Label holder<br>Protective flap   |

## Complementary

|                             |                                                |
|-----------------------------|------------------------------------------------|
| Communication network type  | 1000BASE-TX                                    |
| Communication port protocol | ATM 1200 Mbps                                  |
| Number of modules           | 2 modules                                      |
| Socket number               | 1                                              |
| Type of footprint           | Infraplus                                      |
| Connector type              | S-One                                          |
| Cable shielding type        | STP                                            |
| Organization of wire        | Shielded twisted pair                          |
| Connections - terminals     | Click                                          |
| Device mounting             | Flush                                          |
| Fixing mode                 | Clip-in                                        |
| Installation direction      | Straight                                       |
| Material                    | Thermoplastic ABS-UV stabilised: central plate |
| Depth                       | 40.5 mm                                        |
| Width                       | 45 mm                                          |
| Height                      | 45 mm                                          |
| Embedding depth             | 40.5 mm                                        |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                               |                                           |
|-------------------------------|-------------------------------------------|
| resistance to chemical agents | Resistant to alcohol (70 %)               |
|                               | Resistant to alcohol (96 %)               |
|                               | Resistant to A-Lactic Acid                |
|                               | Resistant to diluted quaternary ammonium  |
|                               | Resistant to diluted bleach               |
|                               | Resistant to diluted ammonia              |
|                               | Resistant to soapy water                  |
|                               | Resistant to crystal cleaner              |
|                               | Resistant to hydrogen peroxide 10 volumes |
|                               | Resistant to hexane                       |

## Environment

|                                       |             |
|---------------------------------------|-------------|
| IP degree of protection               | IP20        |
| IK degree of protection               | IK01        |
| Ambient air temperature for operation | -25...55 °C |
| Ambient air temperature for storage   | -25...55 °C |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 4.500 cm  |
| Package 1 Width              | 4.500 cm  |
| Package 1 Length             | 4.510 cm  |
| Package 1 Weight             | 44.000 g  |
| Unit Type of Package 2       | S01       |
| Number of Units in Package 2 | 20        |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 15.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 1.748 kg  |

## Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 18 |
|----------------------|----|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Lower carbon footprint

0.4 kg CO2 eq.

## Use Better



### Materials and Substances

SCIP Number

89f48f58-8743-4a8c-aad2-c796c3e70cb3

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Free of Substances of Very High Concern above the threshold](#)

## Use Longer



### Lifetime extension

Repair

No

## Use Again



### Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Technical Illustration

Wiring diagram

