



LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
FT	0		T	REVISED PER 0G3B-0956-04	11/22/04

DWN	APVD
SS	GS



- 1

1.27μm [.000050] MIN TIN-LEAD OVER
1.27μm [.000050] MIN NICKEL.
- 2

0.76μm [.000030] MIN GOLD IN LOCALIZED
PLATE AREA, 0.25μm [.000010] MIN
GOLD ON THE REMAINDER ALL OVER
1.27μm [.000050] MIN NICKEL.
- 3

2.54μm [.000100] MIN TIN-LEAD OVER
1.27μm [.000050] MIN NICKEL.
- 4

2.54μm [.000100] MIN TIN OVER
1.27μm [.000050] MIN NICKEL.
- 5

1.27μm [.000050] MIN TIN OVER
1.27μm [.000050] MIN NICKEL.

4	SMALL PACK	2	202236-8
	STANDARD	2	202236-7
	SMALL PACK	5	202236-6
	STANDARD	5	202236-5
3	SMALL PACK	1	202236-4
	SMALL PACK	2	202236-3
	STANDARD	1	202236-2
	STANDARD	2	202236-1
FINISH SOLDER TAB		PACKAGING TYPE	FINISH
			PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
SEE CALL OUT

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.13[.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH
PIN BODY:SEE TABLE

DWN
H MOLL
CHK
J.McCLINTON
APVD
A. BOULLIANNE
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
-

27SEP90
15DEC90
15DEC90

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

PIN ASSEMBLY, LOOSE PIECE,
TYPE III+

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=202236

RESTRICTED TO
-

SCALE
8:1

SHEET
1

OF
1

REV
T