

Specifications

Eaton 38ADMNA10E

Air fuse-link, medium voltage, 10 A, AC 38 kV, 50.8 x 442 mm, back-up, 10E



General specifications

PRODUCT NAME	Eaton Bussmann series medium voltage BS air fuse
CATALOG NUMBER	38ADMNA10E
EAN	5027590478335
UPC	051712794398
PRODUCT LENGTH/DEPTH	527 mm
PRODUCT HEIGHT	102 mm
PRODUCT WIDTH	293 mm
PRODUCT WEIGHT	2110 g
COMPLIANCES	Contact factory

Product specifications

AMPERAGE RATING	10 A
FUSE INDICATOR	Non Indicating
FUSE SIZE	50.8x442 mm
BREAKING CAPACITY	40 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	60 Hz
RATED FREQUENCY - MIN	60 Hz
RELEASE CHARACTERISTIC	E
STANDARD	ANSI
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	No
FUSE DIAMETER	51 mm
INTERRUPT RATING	40 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	51 x 442 mm
MOUNTING METHOD	Clip-in
VOLTAGE RATING	38 kV
TYPE	British style, potential transformer
APPLICATION	Primary side transformer protection
FUSE TYPE	ADMN

Resources

BROCHURES	eaton-bussmann-circuit-protection-brochures-en.pdf
-----------	--

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

