


## FEATURES

- **Polyacrylic Material:** Offers excellent resistance to chemicals and high temperatures, ensuring durability and longevity.
- **Maximum Operating Pressure of 2000 kPa:** Suitable for high-pressure applications, providing reliable sealing.
- **Maximum Operating Temperature of 200 °C:** Capable of withstanding high temperatures, making it ideal for demanding environments.
- **Rotary Speed of 10 m/s:** Supports dynamic applications, maintaining performance under rotational movement.
- **8m Length:** Provides ample material for various sealing needs, enhancing flexibility in use.
- **12.5mm Section:** Ensures a robust seal, suitable for a range of gland and valve sizes.

## RS PRO 8m Polyacrylic Gland Packing, 12.5mm Section

RS Stock No: 606-575



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO gland packing is designed for sealing applications in various industrial environments. Made from durable polyacrylic material, it is ideal for use in high-pressure and high-temperature settings, providing reliable sealing performance. The packing is suitable for both static and dynamic applications, ensuring versatility and efficiency.

## General Specifications

Maximum Operating Pressure	2000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	10 m/s
Section	12.5 mm
Sub Type	Gland Packing

## Mechanical Specifications

Length	8 m
Material	Polyacrylic

## Operation Environment Specifications

Maximum Operating Temperature	200 °C
-------------------------------	--------

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------