



IMPACT

TE Internal #: 2007852-3  
150 Position High Speed Backplane Connector, 15 Row, 10 Column, PCB Mount Header, Vertical, Partially Shrouded, 1.9 mm [.075 in] Centerline, IMPACT

[View on TE.com >](#)

Connectors > PCB Connectors > Backplane Connectors > High Speed Backplane Connectors



Number of Positions: 150  
Row-to-Row Spacing: 1.35 mm [.053 in]  
Mating Alignment: With  
Mating Alignment Type: Polarization  
Number of Rows: 15

Features

Product Type Features

Signal Arrangement	Differential
Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
PCB Connector Type	PCB Mount Header
Shroud Style	Partially Shrouded

Configuration Features

Number of Pairs	50
Number of Ground Positions	50
Number of Signal Positions	100
Stackable	No
Number of Positions	150
Number of Rows	15
Number of Columns	10
PCB Mount Orientation	Vertical
Guide Location	Unguided

Electrical Characteristics

Operating Voltage	30 VDC
Impedance	100 Ω



Signal Characteristics

Data Rate	20 – 25 Gb/s
Number of Differential Pairs per Column	5

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	.76 µm[29.92 µin]
PCB Contact Termination Area Plating Material Thickness	.76 – 1.52 µm[30 – 60 µin]
Contact Shape & Form	Dual Beam
Contact Layout	Inline
Contact Mating Area Plating Material	Gold (Au)
Contact Mating Area Length	5.5 mm[.217 in]
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Type	Pin
Contact Current Rating (Max)	.75 A

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	1.4 mm[.055 in]

Mechanical Attachment

Guide Hardware	Without
PCB Mount Retention	With
Mating Retention	Without
PCB Mount Retention Type	Action/Compliant Tail
Mating Alignment	With
Mating Alignment Type	Polarization
Connector Mounting Type	Board Mount

Housing Features

Number of Shrouded Sides	2
--------------------------	---



End Wall Location	Open
Housing Material	LCP - GF (Liquid Crystal Polymer)
Centerline (Pitch)	1.9 mm[.075 in]

Dimensions

PCB Thickness (Recommended)	1 mm
Connector Width	24.8 mm[.976 in]
PCB Hole Diameter	.39 mm[.015 in]
Connector Height	11.95 mm[.47 in]
Connector Length	18.9 mm[.744 in]
Row-to-Row Spacing	1.35 mm[.053 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL E28476

Packaging Features

Packaging Method	Box & Tube, Package
------------------	---------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2110106-1  
IMP100S,R,RA5P10C,UG,39

Also in the Series | IMPACT



High Speed Backplane Connectors  
(149)

Customers Also Bought



TE Part #1-5406203-2  
MJ,ASSY,4P,8POS,CAT5,PNL TABS,1S  
/T



TE Part #1571983-3  
GDH02STR04=DIP SWITCH



TE Part #2-2347090-1  
SOCKET 4677 DG1.0 FOR ODM



TE Part #2-2351050-5  
LGA4677 TFLM ASSY,W/ COVER



TE Part #2316577-1  
CA, MBXLE TO ET

TE Part #2170106-1  
SFP+ 1x1 Enhanced, Gasket, Press fit

TE Part #2204218-8  
MBXLE R/A HEADER 2ACP + 12S

TE Part #2-2309976-1  
ZSFP+ 1X4 CAGE ASSEMBLY, HS, W /O LP

TE Part #2379420-4  
SOCKET E1 TFLM KIT W/ COVER

TE Part #2336522-4  
C/A, SLIVER 74P, RA - RA, 100OHM, GUIDED

Documents

Product Drawings  
IMP100S,H,V5P10C,UG,OEW39,5.5  
English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_2007852-3\_A.2d\_dxf.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_2007852-3\_A.3d\_igs.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_2007852-3\_A.3d\_stp.zip  
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications  
Application Specification  
English

Agency Approvals  
Agency Approval Document  
English