

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Product name: ECOCOOL S 761 B

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses: Coolant/ Cutting solution

Uses advised against: No uses advised against identified.

1.3 Details of the supplier of the safety data sheet

Manufacturer / Supplier FUCHS LUBRICANTS (UK) PLC.
New Century Street
ST1 5HU Hanley
Telephone: +44 (0) 1782 203700

Contact Person: Product Safety department
E-mail: product.safety@fuchs.com
Telephone: +44 (0) 1782 203700

1.4 Emergency telephone number: UK NHS: Dial 111

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

The product has been classified and labelled as hazardous according to regulation GB-CLP.

Classification according to GB-CLP.

Health Hazards

Skin irritation	Category 2	H315: Causes skin irritation.
Serious eye irritation	Category 2	H319: Causes serious eye irritation.
Skin sensitizer	Category 1	H317: May cause an allergic skin reaction.

Environmental Hazards

Chronic hazards to the aquatic environment	Category 2	H411: Toxic to aquatic life with long lasting effects.
--	------------	--

Hazard summary

Physical Hazards: No data available.

2.2 Label Elements

Product name: ECOCOOL S 761 B

Contains: Isothiazolinone derivative



Signal Words: Warning

Hazard Statement(s): H315: Causes skin irritation.
H319: Causes serious eye irritation.
H317: May cause an allergic skin reaction.
H411: Toxic to aquatic life with long lasting effects.

Precautionary Statements

Prevention: P262: Do not get in eyes, on skin, or on clothing.
P273: Avoid release to the environment.
P280: Wear protective gloves/protective clothing/eye protection/face protection.

Response: P333+P313: If skin irritation or rash occurs: Get medical advice/attention.

Disposal: P501: Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

2.3 Other hazards: By handling of mineral oil products and chemical products no particular hazard is known when normal precautions (item 7) and personal protective equipment (item 8) are kept. The product may not be released into the environment without control.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

General information: Mixture of mineral base oil, anionic and nonionic agents and corrosion preventing additives in combination with stabilizers based on glycol-fatty alcohols. This product is applied only as solution or emulsion in water.

Product name: ECOCOOL S 761 B

Chemical name	Identifier	Concentration *	UK-REACH Registration No.	Notes
sec. alkanolamine, ionic equilibrium with acids	Neutralisation product (*)	5,00% - <10,00%		
acid, ionic equilibrium with organic bases	Neutralisation product (*)	5,00% - <10,00%		
prim. Alkanol amine	EINECS: 204-709-8	1,00% - <5,00%		
Fatty alcohol, ethoxylated	Polymer	1,00% - <2,50%		
acid, ionic equilibrium with organic bases	Neutralisation product (*)	1,00% - <5,00%		
acid, ionic equilibrium with organic bases	Neutralisation product (*)	1,00% - <2,50%		
Isothiazolinone derivative	EINECS: 220-120-9	0,10% - <1,00%		

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

PBT: persistent, bioaccumulative and toxic substance.

vPvB: very persistent and very bioaccumulative substance.

(*) Neutralisation product: Equilibrium of Ionic Pairs in aqueous solution according to GB-REACH Annex V, 4.

Classification

Chemical name	Identifier	Classification
sec. alkanolamine, ionic equilibrium with acids	Neutralisation product (*)	GBCLP: Acute Tox. 3;H301, Acute Tox. 3;H311, Eye Irrit. 2;H319, Skin Irrit. 2;H315, Aquatic Chronic 1;H410, Aquatic Acute 1;H400
acid, ionic equilibrium with organic bases	Neutralisation product (*)	GBCLP: Skin Irrit. 2;H315, Eye Irrit. 2;H319, Aquatic Acute 1;H400
prim. Alkanol amine	EINECS: 204-709-8	GBCLP: Skin Irrit. 2;H315, Eye Irrit. 2;H319, Aquatic Chronic 3;H412
Fatty alcohol, ethoxylated	Polymer	GBCLP: Skin Irrit. 2;H315, Aquatic Chronic 2;H411
acid, ionic equilibrium with organic bases	Neutralisation product (*)	GBCLP: , Eye Irrit. 2;H319
acid, ionic equilibrium with organic bases	Neutralisation product (*)	GBCLP: Eye Irrit. 2;H319, Aquatic Chronic 2;H411
Isothiazolinone derivative	EINECS: 220-120-9	GBCLP: Eye Dam. 1;H318, Skin Irrit. 2;H315, Acute Tox. 4;H302, Skin Sens. 1;H317, Aquatic Acute 1;H400, Acute Tox. 2;H330, Aquatic Chronic 2;H411; M-Factor (aquatic acute): 1; M-Factor (aquatic chronic): 1

GB-CLP

specific concentration limit

Chemical name	Identifier	specific concentration limit	Hazard class	Hazard Category	Hazard statements
Isothiazolinone derivative	EINECS: 220-120-9	>= 0,05 %	Skin sensitizer	1	H317

For the wording of the listed hazard statements refer to section 16.

Please note that the mineral oils and petroleum distillates used in our products are severely refined and have a DMSO extract < 3% as measured by method IP 346 and are not classified as carcinogenic according to Note L of Annex VI of Regulation GB-CLP.

Product name: ECOCOOL S 761 B

SECTION 4: First aid measures

General: Instantly remove any clothing soiled by the product.

4.1 Description of first aid measures

Inhalation: Supply fresh air; consult doctor in case of symptoms.

Eye contact: Immediately flush with plenty of water for at least 15 minutes. If easy to do, remove contact lenses. Get medical attention.

Skin Contact: Get medical attention. Destroy or thoroughly clean contaminated shoes. Immediately remove contaminated clothing and shoes and wash skin with soap and plenty of water. If skin irritation or an allergic skin reaction develops, get medical attention.

Ingestion: Rinse mouth. Call a POISON CENTER or doctor/ physician if you feel unwell.

4.2 Most important symptoms and effects, both acute and delayed: Suspected to cause hypersensitivity and allergy. Causes serious eye irritation. Causes skin irritation.

4.3 Indication of any immediate medical attention and special treatment needed Hand over this safety data sheet to the physician with the special comment "watermiscible cutting oil". Symptoms may be delayed.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media: CO₂, fire extinguishing powder or fog like water spraying. Extinguish larger fires with alcohol resistant foam or spray water with suitable surfactant added

Unsuitable extinguishing media: Water with a full water jet.

5.2 Special hazards arising from the substance or mixture: During fire, gases hazardous to health may be formed.

5.3 Advice for firefighters

Special fire-fighting procedures: Move container from fire area if it can be done without risk. Dispose of fire debris and contaminated fire fighting water in accordance with official regulations. Collect contaminated fire fighting water separately. It must not enter drains.

Special protective equipment for fire-fighters: Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

Product name: ECOCOOL S 761 B

SECTION 6: Accidental release measures

- 6.1 Personal precautions, protective equipment and emergency procedures:** Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Keep unauthorized personnel away. In case of spills, beware of slippery floors and surfaces.
- 6.2 Environmental Precautions:** Avoid release to the environment. Prevent further leakage or spillage if safe to do so. Prevent from spreading (e.g. by binding or oil barriers). Environmental manager must be informed of all major spillages. Do not allow to enter drainage system, surface or ground water.
- 6.3 Methods and material for containment and cleaning up:** Absorb with liquid-binding material (sand, diatomite, acidbinders, universal binders, sawdust). Dispose of the material collected according to regulations. Stop the flow of material, if this is without risk.
- 6.4 Reference to other sections:** See Section 8 of the SDS for Personal Protective Equipment. See Section 7 for information on safe handling See Section 13 for information on disposal.
- Dike for later disposal. Prevent entry into waterways, sewer, basements or confined areas. Stop the flow of material, if this is without risk.

SECTION 7: Handling and storage:

- 7.1 Precautions for safe handling:** Wash hands thoroughly after handling. Do not eat, drink or smoke when working with the product. Take usual precautions when handling mineral oil products or chemical products. Avoid contact with eyes, skin, and clothing. Prevent formation of aerosols. Observe good industrial hygiene practices. Provide adequate ventilation.
- 7.2 Conditions for safe storage, including any incompatibilities:** Local regulations concerning handling and storage of waterpolluting products have to be followed. Store above freezing.
- 7.3 Specific end use(s):** Not applicable
- Storage Class:** 10, Combustible liquids

SECTION 8: Exposure controls/personal protection

8.1 Control Parameters

Occupational Exposure Limits

None of the components have assigned exposure limits.

8.2 Exposure controls

Appropriate engineering controls:

Provide adequate ventilation. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Product name: ECOCOOL S 761 B

Individual protection measures, such as personal protective equipment

General information:	Wash hands before breaks and after work. Use personal protective equipment as required. Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment. The usual precautionary measures should be adhered to in handling the chemicals or the mineral oil products.
Eye/face protection:	Avoid contact with skin and eyes. Goggles/face shield are recommended. If risk of splashing, wear safety goggles or face shield.
Skin protection	
Hand Protection:	Material: Nitrile butyl rubber (NBR). Min. Breakthrough time: ≥ 480 min Recommended thickness of the material: $\geq 0,38$ mm Avoid long-term and repeated skin contact. Suitable gloves can be recommended by the glove supplier. Use skin protection cream for preventive skin protection. Protective gloves, where permitted in acc. to safety directions. The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
Other:	Do not carry cleaning cloths impregnated with the product in trouser pockets. Wear suitable protective clothing.
Respiratory Protection:	Ensure good ventilation/exhaustion at the workplace. Avoid breathing vapour/ aerosol.
Thermal hazards:	Not known.
Hygiene measures:	Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing to remove contaminants. Discard contaminated footwear that cannot be cleaned.
Environmental Controls:	No data available.

SECTION 9: Physical and chemical properties
--

9.1 Information on basic physical and chemical properties

Appearance

Physical state:	liquid
Form:	liquid
Color:	Yellow
Odor:	Characteristic
pH:	9,2 (5 %)
Freezing point:	not determined
Boiling Point:	No data available.
Flash Point:	> 100 °C

Product name: ECOCOOL S 761 B

Evaporation Rate:	Not applicable for mixtures
Flammability (solid, gas):	not determined
Flammability Limit - Upper (%)-:	Not applicable for mixtures
Flammability Limit - Lower (%)-:	Not applicable for mixtures
Vapor pressure:	Not applicable for mixtures
Relative vapor density:	Not applicable for mixtures
Density:	0,94 g/cm ³ (15 °C)
Solubility(ies)	
Solubility in Water:	Emulsifiable in water
Solubility (other):	No data available.
Partition coefficient (n-octanol/water):	Not applicable for mixtures
Autoignition Temperature:	not determined
Decomposition Temperature:	not determined
Flow time	Value not relevant for classification
Explosive properties:	Value not relevant for classification
Oxidizing properties:	Value not relevant for classification
Particle characteristics:	Not applicable
9.2 Other information	No data available.

SECTION 10: Stability and reactivity

10.1 Reactivity:	Stable under normal use conditions.
10.2 Chemical Stability:	Stable under normal use conditions.
10.3 Possibility of hazardous reactions:	Stable under normal use conditions.
10.4 Conditions to avoid:	Stable under normal use conditions.
10.5 Incompatible Materials:	Strong oxidizing substances. Strong acids. Strong bases.
10.6 Hazardous Decomposition Products:	Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapors.

SECTION 11: Toxicological information

Information on likely routes of exposure

Inhalation:	No data available.
Ingestion:	No data available.
Skin Contact:	Causes skin irritation. May cause an allergic skin reaction.
Eye contact:	Causes eye irritation.

Product name: ECOCOOL S 761 B

11.1 Information on toxicological effects

Acute toxicity

Oral

Product:	ATEmix: 3.333 mg/kg
Specified substance(s) sec. alkanolamine, ionic equilibrium with acids	LD 50 (Rat): 200 mg/kg
Isothiazolinone derivative	LD 50 (Rat): 670 mg/kg

Dermal

Product:	ATEmix: 3.333 mg/kg
Specified substance(s) sec. alkanolamine, ionic equilibrium with acids	LD 50 (Rabbit): 200 - 316 mg/kg

Inhalation

Product:	ATEmix: 25,5 mg/l Dust and mist Dust and mist
Specified substance(s) Isothiazolinone derivative	LC 50 (Rat, 4 h): 0,11 mg/l

Skin Corrosion/Irritation:

Product:	Based on available data, the classification criteria are met.
-----------------	---

Serious Eye Damage/Eye Irritation:

Product:	Based on available data, the classification criteria are met.
-----------------	---

Respiratory or Skin Sensitization:

Product:	Skin sensitizer: Based on available data, the classification criteria are met. Respiratory sensitizer: Based on available data, the classification criteria are not met.
-----------------	---

Germ Cell Mutagenicity

Product:	Based on available data, the classification criteria are not met.
-----------------	---

Carcinogenicity

Product:	Based on available data, the classification criteria are not met.
-----------------	---

Reproductive toxicity

Product:	Based on available data, the classification criteria are not met.
-----------------	---

Specific Target Organ Toxicity - Single Exposure

Product:	Based on available data, the classification criteria are not met.
-----------------	---

Specific Target Organ Toxicity - Repeated Exposure

Product:	Based on available data, the classification criteria are not met.
-----------------	---

Aspiration Hazard

Product:	Based on available data, the classification criteria are not met.
-----------------	---

Product name: ECOCOOL S 761 B

Other adverse effects: No data available.

SECTION 12: Ecological information

12.1 Toxicity

Acute toxicity

Product: Based on available data, the classification criteria are not met.

Fish

Specified substance(s)

sec. alkanolamine, ionic
equilibrium with acids LC 50 (Fish, 96 h): 32 - 46 mg/l

prim. Alkanol amine LC 50 (Fish, 96 h): 184 mg/l (OECD 203)

acid, ionic equilibrium
with organic bases LC 50 (Zebra danio (Danio rerio), 96 h): 9,1 mg/l (OECD 203)

Isothiazolinone derivative LC 50 (Fish, 96 h): 2,15 mg/l (OECD 203)

Aquatic Invertebrates

Specified substance(s)

sec. alkanolamine, ionic
equilibrium with acids EC 50 (Water Flea, 48 h): 8 mg/l (OECD 202)

prim. Alkanol amine EC 50 (Water Flea, 48 h): 193 mg/l (OECD 202)

acid, ionic equilibrium
with organic bases EC 50 (Daphnia magna, 48 h): 1,6 mg/l

Isothiazolinone derivative EC 50 (Water Flea, 48 h): 2,9 mg/l (OECD 202)

Chronic Toxicity

Product: Based on available data, the classification criteria are met.

Aquatic Invertebrates

Specified substance(s)

sec. alkanolamine, ionic
equilibrium with acids NOEC (Water Flea, 21 d): 0,016 mg/l (OECD 211)

Isothiazolinone derivative NOEC (Water Flea, 21 d): 1,2 mg/l (OECD 211)

Toxicity to Aquatic Plants

Specified substance(s)

sec. alkanolamine, ionic
equilibrium with acids EC 50 (Alga, 72 h): 0,38 mg/l

prim. Alkanol amine EC 50 (Alga, 72 h): 565,5 mg/l (OECD 201)

acid, ionic equilibrium
with organic bases EC 50 (Green algae (Dunaliella bioculata), 72 h): 5,2 mg/l (OECD 201)
EC 10 (72 h): 0,96 mg/l (OECD 201)

Product name: ECOCOOL S 761 B

Isothiazolinone derivative EC 50 (Alga, 72 h): 0,11 mg/l (OECD 201)

12.2 Persistence and Degradability

Biodegradation

Product:	Not applicable for mixtures
Specified substance(s) sec. alkanolamine, ionic equilibrium with acids	77 % (14 d, OECD 301C) Readily biodegradable
prim. Alkanol amine	89,3 % (28 d, OECD 301F) Readily biodegradable
acid, ionic equilibrium with organic bases	73 % (28 d, OECD 301B) Readily biodegradable

12.3 Bioaccumulative potential

Product:	Not applicable for mixtures
Specified substance(s) prim. Alkanol amine	Bioconcentration Factor (BCF): < 1
acid, ionic equilibrium with organic bases	Fish, Bioconcentration Factor (BCF): 234,67

12.4 Mobility in soil:

Product:	Not applicable for mixtures
-----------------	-----------------------------

12.5 Results of PBT and vPvB assessment:

The product does not contain any substances fulfilling the PBT/vPvB criteria.

12.6 Other adverse effects:

Toxic to aquatic life with long lasting effects.

Water Hazard Class (WGK):

WGK 2: significantly water-endangering.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

General information:	Dispose in accordance with all applicable regulations.
Disposal methods:	Discharge, treatment, or disposal may be subject to national, state, or local laws.

List of Waste (LoW) Codes

12 01 09*: machining emulsions and solutions free of halogens

Product name: ECOCOOL S 761 B**SECTION 14: Transport information****ADR/RID**

14.1 UN number or ID number:	UN 3082
14.2 UN Proper Shipping Name:	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.(sec. alkanolamine, ionic equilibrium with acids)
14.3 Transport Hazard Class(es)	
Class:	9
Label(s):	9
Hazard No. (ADR):	90
Tunnel restriction code:	(-)
14.4 Packing Group:	III
14.5 Environmental hazards:	Dangerous for the environment
14.6 Special precautions for user:	–

IMDG

14.1 UN number or ID number:	UN 3082
14.2 UN Proper Shipping Name:	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.(sec. alkanolamine, ionic equilibrium with acids)
14.3 Transport Hazard Class(es)	
Class:	9
Label(s):	9
EmS No.:	F-A, S-F
14.3 Packing Group:	III
14.5 Environmental hazards:	Marine pollutant
14.6 Special precautions for user:	–

IATA

14.1 UN number or ID number:	UN 3082
14.2 Proper Shipping Name:	Environmentally hazardous substance, liquid, n.o.s.(sec. alkanolamine, ionic equilibrium with acids)
14.3 Transport Hazard Class(es):	
Class:	9
Label(s):	9MI
14.4 Packing Group:	III
14.5 Environmental hazards:	Dangerous for the environment
14.6 Special precautions for user:	–

Amounts up to 5kg or 5 L are not regulated, (ADR/RID SP 375, IMDG 2.10.2.7, IATA SP A197)

14.7 Transport in bulk according to Annex II of MARPOL and the IBC Code: Not applicable.

SECTION 15: Regulatory information**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture:****GB Regulations****The Ozone-Depleting Substances and Fluorinated Greenhouse Gases (Amendment etc.) (EU Exit) Regulations 2019:**

Product name: ECOCOOL S 761 B

none

The Persistent Organic Pollutants (Amendment) (EU Exit) Regulations 2020:

none

15.2 Chemical safety assessment:

No Chemical Safety Assessment has been carried out.

DIRECTIVE Control of Major Accident Hazards Regulations 2015:

The product falls into the scope of the Control of Major Accident Hazards Regulations 2015.

Hazard category in accordance with GB-CLP	Qualifying quantity for the application of Lower-tier requirements:	Qualifying quantity for the application of Upper-tier requirements:
E2: Hazardous to the Aquatic Environment in Category Chronic 2	200 t	500 t

SECTION 16: Other information

Revision Information:

Vertical lines in the margin indicate an amendment.

Wording of the H-statements in section 2 and 3

H301	Toxic if swallowed.
H302	Harmful if swallowed.
H311	Toxic in contact with skin.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H330	Fatal if inhaled.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

Other information:

The classification complies with the current GB lists; however, it has been supplemented with expert literature information and information provided by/about our company. The following evaluation methods were used: On the basis of test data; Calculation Method; Bridging Principle "Substantially similar mixtures"; Expert Judgement

Revision Date:

13.01.2023

Product name: ECOCOOL S 761 B

Disclaimer:

The data contained in this safety data sheet are based on our current knowledge and experience and are given to the best of our knowledge and belief. It characterizes the product only with regard to safety requirements for handling, transport and disposal. The data do not describe the product's properties (tech. product specification). Neither should any agreed property nor the suitability of the product for any specific technical application be deduced from the data contained in this safety data sheet. Modifications on this document are not allowed. The data are not transferable to other products. In the case of mixing the product with other products or in the case of processing, the data in this safety data sheet are not necessarily valid for the new-made material. It is the responsibility of the recipient of the product to observe federal, state and local law. Please contact us to obtain up-to-date safety data sheets. This document was issued electronically and has no signature.