



M18 FUEL 100mm Braking Grinder

M18 FSAG100XB-0X0

- Generates Corded Power - Powerful POWERSTATE Brushless Motor spins at 8,500 RPM and allows the user to complete the toughest grinding and cutting applications
- Fastest Cutting - Increased Productivity; fastest cuts against the competition in 12.7 mm rebar
- RAPIDSTOP Brake, Enhanced Safety - Quickly stops accessories to enhance safety

MODEL VARIANT



INCLUDES

- M18 FSAG100XB (1)
- FIXTEC Nut (1)
- Dynacase (1)
- Safety Guard (1)
- Side Handle (1)

Categories: Grinders

Range Spec



WHAT'S INCLUDED

M18 FSAG100XB-0X0

PRODUCT SPECIFICATIONS	
Length (mm)	333.3
Height (mm)	111.9
Battery platform	M18 REDLITHIUM-ION
Voltage (V)	18
No Load Speed (rpm)	8,500 RPM
Disc diameter (mm)	100
Weight with battery pack if applicable (kg)	2.6 kg (w/5.0Ah battery)