AGILA

2475ETP035S70 12x30

EAN 4031582431599

Swivel castor with wheel brake, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, threaded stem with hexagon neck. Wheel centre made of steel, Tread: Polyurethane, casted, precision ball bearing.

Technical Data

Wheel diameter	35 mm
Wheel width	25 mm
Threaded stem	12 x 30 mm
Offset	13.5 mm
Swivel Interference	62 mm
Overall height	65 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.243 kg
Swivel Radius	31 mm
Hardness of tread	Shore D 42
Load capacity	100 kg
Load capacity (static)	200 kg

Advantages at a glance

Roll performance	●●●●○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●○○

© Copyright 2022 TENTE International **www.tente.com** 24/06/2022