

This document was generated on 10/08/2014 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: <u>43045-1000</u>				1 Ann	
Status:		Active			
Overview: Description:		Micro-Fit 3.0 [™] Connectors Micro-Fit 3.0 [™] Header, Surface Mount Compatible, Dual Row, Right Angle, with Snap- in Plastic Peg PCB Lock, 10 Circuits, Tin (Sn) Plating, Glow Wire Compatible			
	Documents: <u>3D Model</u> <u>Drawing (PDF)</u> Product Specification	<u>PS-43045 (PDF)</u>	Test Summary TS-43045-001 (PDF) RoHS Certificate of Compliance (PDF) Product Literature (PDF)	Series	
Agency Certification		tion			
	CSA TUV UL General Product Family		LR19980 R72081037 E29179 PCB Headers	EU RoHS ELV and RoHS Compliant REACH SVHC Contains SVHC: No Low-Halogen Status	
	Series Application Comments		43045 Power, Wire-to-Board High Temperature Square Pin Solder Type <p><p>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13 b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <p><p> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test</p></p></p></p>	Low-Halogen Need more information on product environmental compliance? Email productcompliance@molex.com For a multiple part number RoHS Certificate of Compliance, click here	
				Please visit the <u>Contact Us</u> section for any non-product compliance questions.	
				Search Parts in this Series 43045Series	
	Overview Product Literature Ord Product Name UPC	der No	standard IEC 60695-2-11 and any applicable product end-use standard(s). <p> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options. <u>Micro-Fit 3.0TM Connectors</u> 987650-5984 Micro-Fit 3.0TM 800754372121</p>	Mates With 43025 Micro-Fit 3.0 [™] Receptacle Housing	
	Physical Breakaway Circuits (Loaded) Circuits (maximum) Color - Resin Durability (mating cyc Flammability Glow-Wire Compliant Mated Height Material - Metal Material - Plating Material	ing	No 10 10 Black 30 94V-0 Yes 10.29mm Brass Tin Tin		

Material - Resin Net Weight Number of Rows Orientation PCB Locator PCB Retention PCB Thickness - Recommended Packaging Type Pitch - Mating Interface Plating min - Mating Polarized to PCB Shrouded Stackable Surface Mount Compatible (SMC) Temperature Range - Operating Termination Interface: Style	High Temperature Thermoplastic 1.677/g 2 Right Angle Yes Yes 1.60mm Tray 3.00mm 0.254µm Yes Fully No Yes -40°C to +105°C Through Hole			
Electrical Current - Maximum per Contact Voltage - Maximum	5A 600V			
Solder Process Data Duration at Max. Process Temperature (seconds) Lead-free Process Capability Max. Cycles at Max. Process Temperature Process Temperature max. C	30 SMC & Wave Capable (TH only) 3 260			
Material Info				
Reference - Drawing Numbers Product Specification Sales Drawing Test Summary	PS-43045, RPS-43045-003, RPS-43045-004 SD-43045-001 TS-43045-001			

This document was generated on 10/08/2014
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION