

Benchmark**BMG784**

ULTRA LIGHTWEIGHT, EXTREME CUT RESISTANT GLOVES WITH NITRILE FOAM

Using the latest innovation, the BMG784 is a very light weight glove (18 gauge) providing outstanding cut protection and high dexterity in the most risky applications. Thin, breathable with a long lasting coating, ideal for all precise applications.

FEATURES

- › Cut resistant: Level F (EN 388:2016)
- › 18 gauge seamless liner offers flexibility, comfort and high fingertip sensitivity
- › HPPE on the inside provides comfort and protection
- › Specific metal fibre and nylon on the outside, fully encapsulated enable extreme cut protection against burrs and sharp edges.
- › Nitrile foam coating gives exceptional grip in oily conditions while allowing warm air and moisture from inside to escape, keeping your hands dry and comfortable
- › Reinforced thumb crotch enhances durability
- › Designed for easy movement and continuous wear
- › Breathable back of hand to reduce perspiration
- › Seamless knit prevents irritation
- › Elasticated wrist provides a secure fit



SUITABLE FOR


Typical Industries

- Automotive
- Construction
- Logistics
- Maintenance
- Manufacturing
- Transport

Suitable Applications

- Assembly
- Handling sharp and greasy parts
- Machining
- Bodywork
- Precision mechanics

CERTIFICATION



See overleaf for explanation

Benchmark**BMG784****PRODUCT INFORMATION**

MATERIALS	LINER:	18 gauge HPPE, metal fiber, nylon
	COATING:	Foam nitrile
COLOUR	Grey/Black	
LENGTH (mm)	250 (Size Dependent)	
CUFF STYLE	Elasticated knit wrist	

ORDERING DETAILS


SIZE	ITEM NO.	PACKAGING
7/S	BMG00784ED	Individually bagged 10 pairs per bag 120 pairs per case
8/M	BMG00784EF	
9/L	BMG00784EH	
10/XL	BMG00784EJ	
11/XXL	BMG00784EL	

RECOMMENDATIONS FOR USE

- **USE:** General handling glove with cut protection. Not suitable for thermal, electrical, chemical protection. Do not use near moving machines if there is a risk of entanglement
- **STORAGE :** Store in dry conditions in the original packaging and away from direct sunlight
- **CLEANING:** To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present
- **LIFETIME:** Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use

CERTIFICATION LEGENDS

MECHANICAL
HAZARDS
EN 388: 2016

PERFORMANCE LEVELS*

* If tests are not performed or are not applicable, 'X' will be placed instead of a number/letter

EUROPE

www.globus.co.uk

E: sales@globus.co.uk

T: +44 (0)161 877 4747

F: +44 (0)161 877 4746

MIDDLE EAST AND AFRICA

www.globusgroup.com/gcc

E: gcc@globusgroup.com

T: +971 4 882 9962

F: +971 4 882 9963



Globus (Shetland) Ltd, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES

© 2020 Globus (Shetland) Ltd | BMK-DATA-BMK784-0620_1