

Item no. 12.02.1002

ROLINE USB 2.0-RS232 Adapter, for DIN Rail, 2P



Features:

- Converter to connect 2 serial devices to a USB port of a Computer
- Mode: Asynchronous serial communication
- Compatible with USB 2.0, USB 1.1, USB 1.0
- Data transfer rate of up to 115.2 Kbit/s
- Signals: TXD, RXD, RTS, CTS, DTR, DSR, DCD, RI , GND
- 15 KV ESD protection for all RS-232 ports
- Connectors: 2x DB9 Male, 1x Mini USB type B
- Status LEDs (TXD, RXD)
- For DIN rail mounting
- Power supply over Mini USB type B connector (max. 40 mA)
- Supported Operating Systems: Windows 98SE/ME/2000/ XP/Vista/ Server 2003/Server 2008/Windows 7

Serial Converter

Mode	Asynchronous serial communication
Speed	Up to 115.2kbps
Connector	2 x DB9 Male
Signals	TXD, RXD, RTS, CTS, DTR, DSR, DCD, RI, GND
Protection	15KV ESD Protection for all signals
Data Bits	7, 8
Stop Bits	1, 2
Flow Control	RTS/CTS,X-On/X-Off
Parity	None, Even, Odd, Space, Mark
IRQ/IO Address	Assigned by BIOS
FIFO	TX Buffer 4k bytes, RX Buffer 4k bytes per channel

No.	DB9 Male
1	DCD
2	RXD
3	TXD
4	DTR
5	GND
6	DSR
7	RTS
8	CTS
9	RI