



HPI

TE Internal #: 1-1735447-4

Housing, Receptacle, Wire-to-Board, 14 Position, 2 mm [.079 in]

Centerline, 1 Row, Natural, Wire & Cable, Power & Signal, HPI

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings > AMP HPI 2.0 mm Receptacle Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **14**

Centerline (Pitch): **2 mm [.079 in]**

[All AMP HPI 2.0 mm Receptacle Housings \(59\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	14
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Layout	Inline
Contact Base Material	Copper Alloy
Contact Type	Socket



Contact Current Rating (Max)	3 A
------------------------------	-----

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
Mating Retention Type	Latch
PCB Mount Retention	Without
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Thermoplastic
Housing Entry Configuration	Both Ends Closed
Centerline (Pitch)	2 mm [.079 in]

Dimensions

Connector Width	9.4 mm [.37 in]
Connector Height	6.55 mm [.258 in]
Wire Size	30 – 24 AWG
Connector Length	28.8 mm [1.134 in]

Usage Conditions

Operating Temperature Range	-25 – 85 °C [-13 – 185 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Bag
Packaging Quantity	600

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1-1735446-4
2MM PITCH HPI POST HEADER,
VERTICAL, 14P

Also in the Series | HPI


 Connector Contacts(1)	 PCB Headers & Receptacles(332)	 Rectangular Connector Housings(51)	 Rectangular Power Connectors(275)
--	--	---	--



Standard Rectangular Connectors(51)



Wire-to-Board Connector Assemblies & Housings(83)



Wire-to-Board Headers & Receptacles (332)

Customers Also Bought




TE Part #1735801-1
2.0mm,Crimp,Contact



TE Part #1-480424-0
04P CMNL PLUG HSG F/H NATL



TE Part #1735446-4
2MM PITCH HPI POST HEADER, VERTICAL, 4P



TE Part #284512-8
8 POS TERMI-BLOK HDR 900 POLAR




TE Part #2199230-3
M.2 0.5PITCH 4.2H KEY B 15U" AU



TE Part #5520250-3
MJ,R/A,6P/6C,PNL STOPS,TRAY



TE Part #163304-2
MATENLOK SOCKET SDW



TE Part #5-5530843-0
CONN SEC II 10 POS 100C/L



TE Part #1735447-4
HPI 2.0 RECEPTACLE HOUSING, 4P



TE Part #7-1393222-2
V23061B1002A301=MINISTARKSTROM

Documents

Product Drawings

HPI 2.0 RECEPTACLE HOUSING, 14P

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1735447-4_F.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_1-1735447-4_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1735447-4_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HPI Connectors QRG](#)

English

Product Specifications

[Application Specification](#)

English