



SAFETY DATA SHEET
FLAWFINDER CLEANER SPRAY
CP0246 v3.1 RS 196-3508

Page 1

Issued: 19/11/2008

Revision No: 5

RS REACH revision date 01/08/10

1. IDENTIFICATION OF THE SUBSTANCE / PREPARATION AND OF THE COMPANY / UNDERTAKING

Product name: FLAWFINDER CLEANER SPRAY
Use of substance / preparation: Solvent cleaner.
Company name: ROCOL
ROCOL House
Swillington
Leeds
West Yorkshire
LS26 8BS
ENGLAND
Tel: +44 (0) 113 232 2700
Fax: +44 (0) 113 232 2740
Emergency tel: +44 (0) 113 232 2600
Email: customer-service@rocol.com

Supplied by:
RS Components Ltd,
Birchington Road, Corby, Northants, NN17 9RS.
Tel: +44 (0) 1536 402888 (8am to 8pm)
Email: technical.help@rs-components.com

2. HAZARDS IDENTIFICATION

Main hazards: Highly flammable. Irritating to eyes and skin. Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. Vapours may cause drowsiness and dizziness.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous ingredients: PROPAN-2-OL 30-60%
EINECS: 200-661-7 CAS: 67-63-0
[F] R11; [Xi] R36; [-] R67

- ISOPARAFFINIC HYDROCARBON 30-60%
EINECS: 292-458-5 CAS: 90622-56-3
[F] R11; [Xn] R65; [Xi] R38; [-] R67; [N] R51/53
- CARBON DIOXIDE AEROSOL PROPELLANT 5-15%
EINECS: 204-696-9 CAS: 124-38-9
[-]

4. FIRST AID MEASURES (SYMPTOMS)

Skin contact: There may be irritation and redness at the site of contact.
Eye contact: There may be irritation and redness. The eyes may water profusely.
Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.
Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

4. FIRST AID MEASURES (ACTION)

Skin contact: Wash immediately with plenty of soap and water.
Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.
Ingestion: Wash out mouth with water. Do not induce vomiting. Consult a doctor.
Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so.

5. FIRE-FIGHTING MEASURES

Extinguishing media: Alcohol resistant foam. Carbon dioxide. Dry chemical powder. Do not use water. Use water spray to cool containers.
Exposure hazards: Highly flammable. Forms explosive air-vapour mixture. In combustion emits toxic fumes of carbon dioxide / carbon monoxide.
Protection of fire-fighters: Wear self-contained breathing apparatus.

[cont...]

SAFETY DATA SHEET
FLAWFINDER CLEANER SPRAY
CP0246 v3.1 RS 196-3508

6. ACCIDENTAL RELEASE MEASURES

- Personal precautions:** Refer to section 8 of SDS for personal protection details. Eliminate all sources of ignition.
- Environmental precautions:** Do not discharge into drains or rivers.
- Clean-up procedures:** Do not use equipment in clean-up procedure which may produce sparks. Mix with sand or vermiculite. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

7. HANDLING AND STORAGE

- Handling requirements:** Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Smoking is forbidden.
- Storage conditions:** Store in cool, well ventilated area. Keep away from sources of ignition. Keep away from direct sunlight. Ensure lighting and electrical equipment are not a source of ignition.
- Suitable packaging:** Must only be kept in original packaging.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

- Hazardous ingredients:** PROPAN-2-OL
WEL (8 hr TWA): 999 mg/m³ WEL (15 min STEL): 1250 mg/m³
- ISOPARAFFINIC HYDROCARBON
WEL (8 hr TWA): 1200 mg/m³
 - CARBON DIOXIDE AEROSOL PROPELLANT
WEL (8 hr TWA): 5000ppm 9150mg/m³ WEL (15 min STEL): 15000ppm 27400mg/m³
- Engineering measures:** Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.
- Respiratory protection:** Respiratory protection not required.
- Hand protection:** Nitrile gloves. Neoprene gloves.
- Eye protection:** Safety glasses with side-shields.
- Skin protection:** Protective clothing.

9. PHYSICAL AND CHEMICAL PROPERTIES

- State:** Aerosol
- Colour:** Colourless
- Odour:** Characteristic odour
- Evaporation rate:** Fast
- Oxidising:** Non-oxidising (by EC criteria)
- Solubility in water:** Miscible
- Viscosity:** Non-viscous
- Flash point°C:** < -20
- Relative density:** 0.74

10. STABILITY AND REACTIVITY

- Stability:** Stable under normal conditions. Stable at room temperature.
- Conditions to avoid:** Direct sunlight. Heat. Sources of ignition.
- Materials to avoid:** Strong oxidising agents. Strong reducing agents.
- Haz. decomp. products:** In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

11. TOXICOLOGICAL INFORMATION

- Hazardous ingredients:** PROPAN-2-OL
IVN RAT LD50 1088 mg/kg
ORL MUS LD50 3600 mg/kg
ORL RAT LD50 5045 mg/kg
SCU MUS LDLO 6 gm/kg
- Routes of exposure:** Refer to section 4 of SDS for routes of exposure and corresponding symptoms.

12. ECOLOGICAL INFORMATION

Mobility: Highly volatile.
Persistence and degradability: Only slightly biodegradable.
Bioaccumulative potential: No data available.

13. DISPOSAL CONSIDERATIONS

Disposal operations: D5 Specially engineered landfill (e.g. placement into lined discrete cells which are capped and isolated from one another and the environment, etc.).
 R1 Solvent reclamation/regeneration.
Waste code number: kk
Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.
NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

14. TRANSPORT INFORMATION

ADR / RID

UN no: 1950 **ADR Class:** 2
Classification code: 5F
Shipping name: AEROSOLS
Labelling: 2.1



IMDG / IMO

UN no: 1950 **Class:** 2
EmS: F-D,S-U **Marine pollutant:** .
Labelling: 2.1

IATA / ICAO

UN no: 1950 **Class:** 2
Labelling: 2.1

15. REGULATORY INFORMATION

Hazard symbols: Highly flammable.
 Irritant.
 Dangerous for the environment.



Risk phrases: R11: Highly flammable.
 R36/38: Irritating to eyes and skin.
 R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
 R67: Vapours may cause drowsiness and dizziness.

Safety phrases: S16: Keep away from sources of ignition - No smoking.
 S23: Do not breathe spray.
 S51: Use only in well-ventilated areas.
 S24/25: Avoid contact with skin and eyes.
 S35: This material and its container must be disposed of in a safe way.

SAFETY DATA SHEET
FLAWFINDER CLEANER SPRAY
CP0246 v3.1 RS 196-3508

Precautionary phrases: Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

Do not spray on a naked flame or any incandescent material. Keep away from sources of ignition - No smoking. Keep out of the reach of children.

Haz. ingredients (label): PROPAN-2-OL; ISOPARAFFINIC HYDROCARBON

Note: The regulatory information given above only indicates the principal regulations specifically applicable to the product described in the safety data sheet. The user's attention is drawn to the possible existence of additional provisions which complete these regulations. Refer to all applicable national, international and local regulations or provisions.

16. OTHER INFORMATION

Other information: EC Directive 1999/45/EC relating to the classification, packaging and labelling of dangerous preparations.
 EC Directive 91/155/EEC defining the laying down and detailed arrangements for the system of specific information relating to dangerous preparations.
 EC Directive 94/1/EC adapting some technicalities of Council Directive 75/324/EEC on the approximation of the laws of Member States relating to aerosol dispensers.

Risk phrases used in s.3: R11: Highly flammable.
 R36: Irritating to eyes.
 R67: Vapours may cause drowsiness and dizziness.
 R65: Harmful: may cause lung damage if swallowed.
 R38: Irritating to skin.
 R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
 None

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.