

Threaded Rod Cutter LXT®

DSC102

18V • M6 – M10

Brushless cutter for spark-free and neat cutting of steel rods

Quick and silent steel rod cutter with a brushless motor. Cuts steel rods neatly and safely without sparks. Generates burr-free cuts that allow for easy nut tightening.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Cutting Capacity Mild Steel (up to 400N/mm ²)	M6 - M10 mm
Cutting Capacity Stainless Steel (up to 600N/mm ²)	M6 - M8 mm
Sound Pressure Level (L _{pA})	71 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Product Dimensions (L x W x H):	199 x 103 x 308 mm
Tool weight with battery	2,8 - 3,2 kg

User benefits

- Brushless maintenance-free and long-life motor
- No dust, no sparks.
- Single LED job light illuminates the work area
- Electric brake for maximum productivity and increased operator safety
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

783202-0

Hex Wrench 4Mm



821551-8

Makpac case (3)



Other

User manual

Parts drawing