

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: brennenstuhl

Supplier's address: Info, Seestraße 1-3, 72074 Tübingen Tübingen, DE

Model identifier: 1171250747

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	DLS
Light source cap-type (or other electric interface)	N/A		
Mains or non-mains:	MLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	No

Product parameters


Parameter		Value	Parameter	Value
General product parameters:				
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer		150	Energy efficiency class	D
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)		17 500 in Wide cone (120°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	6 500
On-mode power (P_{on}), expressed in W		150,0	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal		-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	80
Outer dimensions without separate control gear, lighting control	Height	261	Spectral power distribution in the range 250 nm to 800 nm, at full-load	See image in last page
	Width	436		
	Depth	364		

parts and non-lighting control parts, if any (millimetre)				
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-	
		Chromaticity coordinates (x and y)	0,313 0,337	
Parameters for directional light sources:				
Peak luminous intensity (cd)	7 500	Beam angle in degrees, or the range of beam angles that can be set	115	
Parameters for LED and OLED light sources:				
R9 colour rendering index value	10	Survival factor	0,90	
the lumen maintenance factor	0,96			
Parameters for LED and OLED mains light sources:				
displacement factor (cos ϕ_1)	0,90	Colour consistency in McAdam ellipses	6	
Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage.	-(b)	If yes then replacement claim (W)	-	
Flicker metric (Pst LM)	1,0	Stroboscopic effect metric (SVM)	0,9	

(a) '-': not applicable;

(b) '-': not applicable;


Spectrum



Spectral Distribution

EPREL registration number: 1536115

Model placed on the Union market from 10/07/2023.



<https://eprel.ec.europa.eu/qr/1536115>

Supplier: Hugo Brennenstuhl GmbH & Co. Kommanditgesellschaft (Manufacturer)

Website: www.brennenstuhl.com

Customer care service:

Name: Info

Website: www.brennenstuhl.com

Email: info@brennenstuhl.de

Phone: +49707188010

Address:

Seestraße 1-3
72074 Tübingen
Germany