



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Manual
Tooling Type	Ergocrimp Hand Tool Assembly or Die

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (.35% in Component Part)



Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-M8793-T273 MQS, RECEPTACLE AND TAB	 TE Part # 1376235-1 MQS SOCKET HSG 3P ASSY	 TE Part # 5-963727-5 MQS SOCKET CONTACT SWS	 TE Part # 5-963727-1 MQS SOCKET CONTACT SWS
 TE Part # 5-963727-6 MQS SOCKET CONTACT SWS	 TE Part # 963728-1 MQS PIN CONTACT SWS	 TE Part # 2-963728-2 LP MQS PIN EDS SANTOVAC	 TE Part # 5-962886-3 MQS0,63 Ag tab LL EDS 0,2-0,5
 TE Part # 963728-3 MQS STIFT-KONT EDS	 TE Part # 963728-2 MQS PIN CONTACT SWS	 TE Part # 6-962885-6 MQS BUCHS-KONT EDS	



Customers Also Bought



TE Part #2-1579016-1
ERGOCRIMP DIE SET MCON 1.2CB
0,5-0,75



TE Part #539953-2
ERGO DIE MCP 4,8K



TE Part #539635-1
ERGO HAND TOOL FRAME-NO DIES



TE Part #4-1579001-7
ERGO DIE SET MCON1.2LL SWS/TAB
SWS



TE Part #3-1579014-9
HAND TOOL MQS 0.13-0.17 SQ.MM



TE Part #539682-2
ERGOCRIMP DIE SET MQS



TE Part #4-1579001-6
ERGO DIE MCP 1,2 LL EDS



TE Part #5-1579001-1
ERGO DIE MQS 0,5-0,75



TE Part #539955-2
ERGO DIE MCP 4,8K E



TE Part #3-1579021-7
ERGO_F.MCP6.3/4.8

Documents

Product Drawings

ERGO DIE MQS

English

Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (non U.S.)

German

