



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (3% in plating) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #2-531803-2
MINI BX PIN HDR 128 POS



TE Part #133611-E
MJ LSS ** 8 8 *** STP * 30 * J 3 2034



TE Part #3-1617118-1
J1MACDD-26XM = M39016/24-030M




TE Part #1-1617119-9
J1MAWD-5XM = M39016/23-013M



TE Part #254960-E
STVE 160 F ABCDE VVVV 7-00 EEUE
17,0 *



TE Part #NB19642001
RNF-100-3/32-BK-STK



TE Part #9-1617591-5
JMGAT-18MW=M28776/6-011M



TE Part #YDTS26W25-29PAV001
PLUG ASSY



TE Part #1757828-2
AMPLIMITE,RCPT ASY,POSTD,109,ZN,
2



TE Part #2-1879216-9
CPF0402 110K 0.1% 25PPM 1K RL

Documents

Product Drawings

MINI-BX RCPT 128P UNSEAL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-530745-1_AC.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-530745-1_AC.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-530745-1_AC.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



English

Japanese

[AMPMODU Connectors and AMP Box Contact Connectors](#)

English