

# SPRING TERMINAL, BASIC DISCONNECT TERMINAL, 3 POINTS, 4MM<sup>2</sup>, GREY

Local distributor code: 397147029 NSYTRR23TB

! Discontinued on: 30 Jun 2024

! To be discontinued

EAN Code: 3606480532962

### Main

Range	Linergy
product name	Linergy TR
Product or component type	Terminal block
Device short name	TRR
Terminal block type	Removable carrier disconnect
Associated connection component	Blade Diode Cylindrical fuse
Terminal block level	1
Mounting mode	Clip-on
Nominal cross section	2.5 mm <sup>2</sup>
Length	72 mm
Colour	Grey
Quantity per set	Set of 50

## Complementary

Fuse size	5 x 20 mm 6 x 32 mm	
	6 X 32 mm	
Width	5.2 mm	
Height	36.5 mm	
Connections - terminals	1 x spring terminal: upstream	
	2 x spring terminal: downstream	
number of connections	3	
Connection position	Тор	
Number of measurement input	2	
Cable cross section	0.082.5 mm², flexible without cable end 0.84 mm², solid	
Wire stripping length	10 mm	
Tool type	Disconnection: flat screwdriver	
	Connection: flat screwdriver	
[Ue] rated operational voltage	400 V conforming to EN/IEC 60947-7-1	
	300 V cURus	
	300 V CSA	

[In] rated current	20 A conforming to EN/IEC 60947-7-1 16 A CSA 16 A UL	
Material	Polyamide 6/6: insulating case	
Dielectric loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4	
Dielectric constant	3.7 at 1 MHz	
Resistivity	10000 M $\Omega$ .m conforming to IEC 60093 10000 M $\Omega$ .m conforming to VDE 0303-T30	
Surface resistance	1000 G $\Omega$ conforming to IEC 60093 1000 G $\Omega$ conforming to VDE 0303-T30	
Creep resistance	500 CTI (> 400 kB) conforming to IEC 60093 500 CTI (> 400 kB) conforming to VDE 0303-T30	
Flame retardance	V0, thickness0.8 mm conforming to UL 94	
Product weight	8.6 g	
Range compatibility	PrismaSeT G PrismaSeT P PrismaSet HD PrismaSeT Pack 250 PanelSeT Mureva TeSys	
Product compatibility	Spacial enclosures	

## **Environment**

Product certifications	CSA UL	
Dielectric strength	1000 V conforming to IEC 60243-1	
Ambient air temperature for operation	-40130 °C conforming to IEC 60216-1 -40130 °C conforming to VDE 0304-T21	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	7.000 cm
Package 1 Length	27.000 cm
Package 1 Weight	9.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	5.000 cm
Package 2 Width	7.000 cm
Package 2 Length	27.000 cm
Package 2 Weight	478.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	300
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm

Package 3 Length	40.000 cm
Package 3 Weight	3.258 kg

# **Logistical informations**

Country of origin

DF

## **Contractual warranty**

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	5
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
China RoHS Regulation	China RoHS declaration

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product
Take-back	No