



Upright Cleaner LXT®

DVC560

18V X 2 • 120 mbar • HEPA filter •
5 L

Powerful brushless upright cleaner powered by 18V X2 batteries

Upright cleaner equipped with powerful brushless motor. Powered by 18V X2 LXT® batteries. Efficient HEPA filter, same high dust pick-up performance than in same AC powered models and 5 L dust capacity. 3 modes for suction power. Telescopic hose / aluminum pipe. LED light.



Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Brushless Motor	✓
Air volume	1,9 m³/min
Max. sealed suction	120 mbar
Dust Bag Capacity	5,0 L
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Noise Uncertainty (K Factor)	2,5 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s²
Vibration Uncertainty (K Factor)	1,5 m/s²
Tool weight with battery	8,3 - 9,0 kg
Product Dimensions (L x W x H):	326 x 318 x 1146 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Working width	318 mm
Suction power	25 / 50 / 85 W
Continuous use 18V / 6.0 Ah x2	120 / 60 / 30 min

User benefits

- Low noise mode for use in noise sensitive environments such as offices, hospitals etc.
- Two separate BL motors, one for vacuuming and the other for rotating brush-roll
- 3 modes for suction power with mode memory function
- Brush roll height adjustable by 4 stages
- HEPA Filter is used to capture very fine particles effectively
- Possibility to tilt main body up to 90 degrees, making it possible to clean even in narrow spaces
- Removable aluminium pipe with integrated handle for cleaning in corners or confined spaces
- LED light illuminates the work site
- Carry handle for easy transportation
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

140H94-2

Soft Brush 360 Complete Set, Blue



140H95-0

Seat Nozzle, Ø32 Mm



191T96-3

Filter Bag Set for Upright Vacuum



199038-1

Seat Nozzle Set 175 mm



199041-2

Seat nozzle set



416041-0

Sash Nozzle 160 x 30 mm



459056-4

Floor Mat Nozzle 120 x 28mm



Other

User manual

Parts drawing