



3669 - EXTENDED STUD ELBOW, BSP PARALLEL AND METRIC



maximum working pressure	30 bar 3 MPa 435 psi
working temperature	-25 to 150 °C -13 to 302 °F 248 to 423 °K
vacuum capability	755 mm Hg
body	FDA CHEMICAL NICKEL PLATED BRASS
sub-base	FDA CHEMICAL NICKEL PLATED BRASS
'O'-rings	FKM
collar	FDA CHEMICAL NICKEL PLATED BRASS
sealing washer	FDA CHEMICAL NICKEL PLATED BRASS

Part Nb	ØD (MM)	C	E (mm)	F (mm)	ØG (mm)	H (mm)	J (mm)	L (mm)	(kg)
	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>
3669 04 10	4	G1/8	5.5	13	10	25.5	7	18	.017
3669 04 19	4	M5x0,8	3.5	10	10	27.5	7	18	.014
3669 06 10	6	G1/8	5.5	13	12	31	8	21.5	.024
3669 06 13	6	G1/4	6.5	16	12	30.5	8	21.5	.028
3669 08 10	8	G1/8	5.5	14	15	33.5	10	23.5	.031
3669 08 13	8	G1/4	5.5	16	15	34	10	23.5	.035
3669 10 13	10	G1/4	6.5	18	17.5	42	12	29	.052
3669 10 17	10	G3/8	7.5	20	17.5	41	12	29	.056
3669 12 13	12	G1/4	6.5	20	19.5	47	15	31	.07
3669 12 17	12	G3/8	7.5	20	19.5	46	15	31	.341
3669 14 21	14	G1/2	9	24	21.5	49	16	34	.094