

# SACC-DSI-M8MS-8CON-M8-L180 SH - Device connector rear mounting



1424236

<https://www.phoenixcontact.com/in/products/1424236>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, Universal, 8-position, Pin, straight, M8, Rear mounting, M8 x 1, Wave soldering

## Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- Standard pin assignments and codings for signal transmission with a uniform design-in design
- For high transmission reliability: optional shield connection to the housing and latching on the PCB

## Commercial data

Item number	1424236
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	ABQ
Product key	ABQJAA
Catalog page	Page 229 (C-2-2013)
GTIN	4046356712484
Weight per piece (including packing)	6.165 g
Weight per piece (excluding packing)	6.165 g
Customs tariff number	85366990
Country of origin	DE

# SACC-DSI-M8MS-8CON-M8-L180 SH - Device connector rear mounting



1424236

<https://www.phoenixcontact.com/in/products/1424236>

## Technical data

### Mounting

Mounting type	Rear mounting M8 x 1 With flat nut
Assembly note	With flat nut

### Product properties

Product type	Circular connectors (device side)
Sensor type	Universal
Number of positions	8
Shielded	yes
Coding	A
Thread type	M8

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

### Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	30 V AC
	30 V DC
Nominal current $I_N$	1.5 A

### Connection data

#### Conductor connection

Connection method	Wave soldering
Contact connection type	Pin
Tightening torque	1 Nm ... 1.5 Nm (Installation-side)

### Connector

#### Connection 1

# SACC-DSI-M8MS-8CON-M8-L180 SH - Device connector rear mounting



1424236

<https://www.phoenixcontact.com/in/products/1424236>

Head design	Pin
Head cable outlet	straight
Head thread type	M8

## Cable/line

Signal type/category	Universal
----------------------	-----------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation)	-40 °C ... 85 °C
	-25 °C ... 85 °C

## Standards and regulations

### M8

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104


# SACC-DSI-M8MS-8CON-M8-L180 SH - Device connector rear mounting

1424236

<https://www.phoenixcontact.com/in/products/1424236>

## Drawings

Schematic diagram



M8 plug pin assignment, 8-pos., view of pin side


# SACC-DSI-M8MS-8CON-M8-L180 SH - Device connector rear mounting




1424236  
<https://www.phoenixcontact.com/in/products/1424236>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1424236>

 <b>cUL Recognized</b> Approval ID: E221474-20070307				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	30 V	1.5 A	26 - 26	-

 <b>UL Recognized</b> Approval ID: E221474-20070307				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	30 V	1.5 A	26 - 26	-

<b>cULus Recognized</b>				
-------------------------	--	--	--	--

# SACC-DSI-M8MS-8CON-M8-L180 SH - Device connector rear mounting



1424236  
<https://www.phoenixcontact.com/in/products/1424236>

## Classifications

### ECLASS

ECLASS-13.0	27440109
-------------	----------

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSI-M8MS-8CON-M8-L180 SH - Device connector rear mounting



1424236

<https://www.phoenixcontact.com/in/products/1424236>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	8b886aaa-f71f-429d-abdd-8ee0c55823f1

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)