


6-line low capacitance IPAD™ for micro-SD card with EMI filtering and ESD protection

Datasheet – production data



Features

- EMI low-pass filter
- ESD protection ± 8 kV (IEC 61000-4-2)
- 208 MHz clock frequency compatible with SDR104 mode (SD3.0)
- Optimized PINOUT for easy PCB layout
- Lead-free package

Benefits

- Low power consumption
- Easy pins access (no tracks between bumps) for easy PCB layout
- 16 Bumps WLCSP package (with 400 μ m pitch) featuring natural PCB routing, cost optimization and saving space on the board
- High reliability offered by monolithic integration
- Reduction of parasitic elements thanks to CSP integration

Complies with the following standards:

- IEC 61000-4-2 level 4:
 - ± 15 kV (air discharge)
 - ± 8 kV (contact discharge)

Applications


- Consumer and computer electronics with micro-SD card such as:
 - Tablet and smartphone
 - HD set-top boxes
 - Camera
 - Notebook
 - Game console
 - Mother boards

Description

The EMIF06-USD14F3 is a 6-line EMI filter dedicated to SD, mini-SD and micro-SD card applications.

This filter includes ESD protection circuitry, which prevents damage to the protected device when inserting the card. Pull-up resistors are not integrated inside the chip, hence the EMIF06-USD14F3 gives the flexibility to customers to use controllers with embedded resistance. This 6-line IPAD™ is packaged into a flip-chip solution, saving PCB space.

Figure 1. Pin configuration (bump side)



™: IPAD is a trademark of STMicroelectronics

1 Characteristics

Table 1. Absolute maximum ratings ($T_{amb} = 25\text{ }^{\circ}\text{C}$)

Symbol	Parameter	Value	Unit		
V_{PP}	ESD discharge IEC 61000-4-2, level 4 (on pins Vcc, SDclk, SDcmd, SDdat0, SDdat1, SDdat2, SDdat3 Air discharge, external pins	15	kV		
	Contact discharge, external pins	8			
	ESD discharge IEC 61000-4-2, level 1 (on pins dat0, dat1, clk, cmd, dat3, dat2) Air discharge, internal pins	2			
	Contact discharge, internal pins	2			
	T_j	Maximum junction temperature		125	$^{\circ}\text{C}$
	T_{op}	Operating temperature range		-30 to +85	$^{\circ}\text{C}$
T_{stg}	Storage temperature range	-55 to +150	$^{\circ}\text{C}$		

Figure 2. EMIF06-USD14F3 schematic




Table 2. Pin configuration

Pin	Signal	Pin	Signal
A1	dat0	C1	Cmd
A2	dat1		
A3	SDdat1	C3	GND
A4	SDdat0	C4	SDcmd
B1	clk	D1	dat3
B2	V _{CC}	D2	dat2
B3	GND	D3	SDdat2
B4	SDclk	D4	SDdat3

Table 3. Electrical characteristics (values, T_{amb} = 25 °C)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
V _{BR}	Breakdown voltage	I _R = 1 mA	14		20	V
I _{RM}	Leakage current	V _{RM} = 3 V			100	nA
R	Serial resistance	Tolerance ±10%, matching ±2%		40		Ω
C _{line}	Data line capacitance	V _{BIAS} = 0V, F = 10 MHz, V _{OSC} = 30mV _{RMS}		10	12	pF
		V _{BIAS} = 1.8V, F = 10 MHz, V _{OSC} = 30 mV _{RMS}		7.5	10	

Figure 3. Electrical characteristics (definitions)




Figure 4. Attenuation versus frequency




Figure 5. Analog crosstalk versus frequency




Figure 6. ESD response to IEC 61000-4-2 (+8 kV contact discharge)




Figure 7. ESD response to IEC 61000-4-2 (-8 kV contact discharge)





Figure 8. Line capacitance versus frequency and bias voltage (typical values)




2 Package information

- Epoxy meets UL94, V0
- Lead-free package

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

2.1 Flip-Chip package information

Figure 9. Flip-Chip package outline



2.2 Packing information





Figure 12. Tape and reel specification



3 Ordering information

Figure 13. Ordering information scheme




Table 4. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
EMIF06-USD14F3	LH	Flip Chip	2.6 mg	5000	Tape and reel 7"

Note: More information is available in the STMicroelectronics Application notes:
 AN2348: "Flip Chip: Package description and recommendations for use"
 AN1751: "EMI Filters: Recommendations and measurements"
 AN4541: "EMI Filters for SD3.0 card: High speed SD card protection and filtering devices"

4 Revision history

Table 5. Document revision history

Date	Revision	Changes
17-Dec-2015	1	First issue.

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2015 STMicroelectronics – All rights reserved