

STHT37230-0

STANLEY® CONTROL-LOCK™ 3m (19mm Wide) Tape Measure

STANLEY®

3253560372309



Product Description :

Lightweight and compact with a rubber over-moulded case the STANLEY® CONTROL-LOCK™ 3M (19mm wide) Tape Measure is ergonomically designed to ensure both comfortable grip and convenient use whilst delivering pro grade durability and extended reach in a compact design. The tape measure features a 19mm blade width and a strong reach of 2.7 metres. The first eight centimetres of the blade have been treated with a durable BladeArmor® coating for better resistance to abrasion or breakage. Furthermore, the blade features a double-sided print to allow quick and easy overhead measurements. STANLEY® CONTROL-LOCK™ 3M tape comes with a multi-catch hook for better grip and ultimate versatility for use on all surfaces.

Product Features and Benefits :

- NEW COMPACT & LIGHTWEIGHT DESIGN for better grip and added comfort and usability.
- INTEGRATED FINGER BRAKE for ultimate control ensuring more controlled measurements and longer tape's life.
- DOUBLE-SIDED BLADE PRINT facilitates awkward or overhead measurements.
- IMPROVED BLADE DURABILITY: First 8cm treated with BladeArmor® coating to reinforce the most vulnerable part of the blade and reduce the risk of kinks or tears.
- GREATER REACH: 19mm blade width and extended reach to help you measure confidently from a distance, even when working alone.
- DETACHABLE MAGNET AND MULTI-CATCH HOOK ensure ultimate versatility for use on all surfaces.
- PORTABILITY: Can be easily secured to a belt, pocket, or waistband using the integral belt clip.
- DURABLE, RUBBER-OVERMOULDED CASE to help withstand multiple drops at the jobsite.
- CLASS II ACCURACY suitable for most professionals, providing a reassuring +/-0,5mm error tolerance at 1m.

Product Warranty :

1 Year Warranty

Product standards and norms :

- MID 2014/32/EU

Technical specifications :

- Blade Width [Metric] : 19 mm
- Blade Length [Metric] : 3 m

