




PIDG

TE Internal #: 32456
Hook Tongue Terminal, 22 AWG, #8 / M4 Stud, 4.17 mm [.164 in]
Stud Diameter, Closed Barrel, Straight, Tin Plating, Partially
Insulated, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals



Ring Terminal Product Type: **Hook Tongue Terminal**

Wire Size: **509 – 3260 CMA**

Stud Size: **#8, M4**

Features

Product Type Features

Ring Terminal Product Type	Hook Tongue Terminal
Stud Size	#8, M4
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Body Features

Insulation Sleeve Color	Red
Stripe Color	Red

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	4.17 mm[.164 in]
Tongue Thickness	.84 mm[.033 in]
Product Length	22.32 mm[.879 in]
Compatible Insulation Diameter (Max)	3.56 mm[.14 in]
Compatible Insulation Diameter Range	2.67 – 3.56 mm[.105 – .14 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2392021-1 RED BATTERY DAHT KIT 110V (47689-4)	TE Part # 539691-2 ERGO DIE R.B.Y	TE Part # 169404 CERTI-LOK DIE	TE Part # 2063030-1 SDE DIESET, RBY, UL
TE Part # 59300 T-HEAD PIDG PG 26-16 ASSY	TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	TE Part # 525690 DAHT PG PIDG 20-18 ASSY	TE Part # 169400 CERTI-LOK FRAME W/O DIES
TE Part # 59250 T-HEAD PIDG 26-14 ASSY	TE Part # 47386 DAHT PG PIDG 26-16 ASSY	TE Part # 47386-4 DAHT PG PIDG 26-16 ASSY	TE Part # 47806-2 DIES PIDG 22-16 DIE SET



TE Part # 2392021-2
RED BATTERY DAHT KIT 220V (47689-4)

TE Part # 58423-1
DIE, RBY IS9252

TE Part # 58433-3
PRO CR ASSY, RBY IS9252

Also in the Series | PIDG

Compression Connectors(17)

Crimp Wire Pins, Tabs & Ferrules(41)

Knife Disconnects(11)

Quick Disconnects(38)

Ring Terminals(588)

Spade Terminals(228)

Special Purpose Terminals(1)

Splices(41)

Customers Also Bought

TE Part #2330274-3
SSRDC-200D40 = Hokey Puck,40A, 200V DC

TE Part #3573650001
TMS-SCE-3/16-2.0-S1-9

TE Part #890036-000
S1009-KIT-A

TE Part #YD369-HR33-NP00000
369 HARSH 3 WAY REC, PIN - BACC65CR1PN

TE Part #740072-000
SO63-3-01

TE Part #ZPF000000000004365
81539-23

TE Part #CAT-P592-F614
PIDG Flanged Spade Tongue Terminals

TE Part #3-6609987-6
15SRBS8=F8222H



Documents

Product Drawings

PIDG HK 22-16 COMM 22-18 MIL 8

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_32456_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_32456_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_32456_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English