

LH-SETH 200K-ST

Pressed steel swivel castor, heavy duty design, with top plate fitting, with brake system 'stop-top', heavy duty wheel, with Blickle Extrathane® polyurethane tread, with welded steel wheel centre

EAN 4047526051600

ID 51607

Customs tariff number 87169090



Bracket: LH series

- strong pressed steel, zinc-plated, blue-passivated, Cr6-free
- heavy fork and top plate
- double ball bearing in the swivel head
- bolted and secured central kingpin, extremely strong
- particularly resistant to shocks and impact due to **four specially-shaped, hardened bearing seats**

Wheel: SETH series

- tread: high-quality polyurethane elastomer Blickle Extrathane®, hardness 92 Shore A, colour yellow, non-marking, non-staining
- wheel centre: thick-walled pressed steel, triple welded, with tubular steel hub, lacquered, colour silver

Other features:

- high chemical resistance to many aggressive substances
- operating temperature: -20 °C to +70 °C, temporarily up to +90 °C, reduced load capacity over +40 °C

Technical data:

Wheel Ø (D)	☉	200 mm
Wheel width	⊥	50 mm
Load capacity at 4 km/h	⚖	900 kg
Load capacity (static)	⚖	2,250 kg
Bearing type	⦿	ball bearing
Total height (H)	⊕	245 mm
Mounting type		top plate
Plate size	📏	140 x 110 mm
Bolt hole spacing	📏	105 x 75–80 mm
Bolt hole Ø	🔧	11 mm
Offset (F)	📏	67 mm
Temperature resistance min		-20 °C
Temperature resistance max		70 °C
Tread and tyre hardness		92 Shore A
Unit weight	⚖	5.6 kg
Non-marking		✓
Non-staining		✓
Antistatic	⚡	×
ESD		×
Electrically conductive	⚡	×
Corrosion-resistant		×
Heat-resistant	🔥	×



Tread and tyre hardness

■■■■■□ 92 Shore A

Rolling resistance



■■■■■□ very good

Wear resistance

■■■■■□ excellent

Operating noise / floor surface preservation

■■■■■□ good



Tread hydrolysis-resistant	×
Suitable for autoclaves	×
Suitable for machine washing	×

Product references



Corresponding fixed castor BH-SETH 200K



Corresponding swivel castor LH-SETH 200K



Wheel used SETH 200/20K