


O5H503



Diffuse reflection sensor with background suppression

O5H-FPKG/2M



- 1 programming buttons
2 When a M5 mounting screw is used, the max. tightening torque is 2 Nm.
receiver in upper lens
transmitter in lower lens



Product characteristics		
Type of light		red light
Housing		rectangular
Application		
Special feature		Background suppression
Function principle		Diffuse reflection sensor
Electrical data		
Operating voltage	[V]	10...36 DC
Current consumption	[mA]	25
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	624
Outputs		
Electrical design		PNP



Diffuse reflection sensor with background suppression

O5H-FPKG/2M

Output function	light-on/dark-on mode; (programmable)	
Max. voltage drop switching output DC [V]	2.5	
Permanent current rating of switching output DC [mA]	200	
Switching frequency DC [Hz]	1000	
Short-circuit protection	yes	
Type of short-circuit protection	pulsed	
Overload protection	yes	
Detection zone		
Range [mm]	50...1800; (white paper 200 x 200 mm 90% remission)	
Range on white object (90 % remission) [mm]	50...1800	
Range on grey object (18 % remission) [mm]	50...900	
Range on black object (6 % remission) [mm]	50...600	
Range adjustable	yes	
Max. light spot diameter [mm]	50	
Light spot dimensions refer to	Range	
Background suppression available	yes	
Operating conditions		
Ambient temperature [°C]	-25...60	
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
MTTF [years]	360	
Mechanical data		
Weight [g]	142	
Housing	rectangular	
Dimensions [mm]	56 x 18.2 x 46.8	
Materials	housing: PA; bezel: stainless steel; operator interface: TPU	
Lens material	PMMA	
Lens alignment	side lens	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Teach function	yes	
Electronic lock	yes	
Remarks		
Remarks	operating voltage "supply class 2" according to cULus	
Pack quantity	1 pcs.	




Diffuse reflection sensor with background suppression

O5H-FPKG/2M

Electrical connection


Cable: 2 m, PUR; 3 x 0.34 mm²

Connection



Core colours :
 BK = black
 BN = brown
 BU = blue

Diagrams and graphs




a: sensor
 b: object
 c: background
 x: distance sensor/object [mm]
 y: min. distance object/background [mm]



Diffuse reflection sensor with background suppression

O5H-FPKG/2M

accuracy graph



x: distance sensor/object [mm]

y: min. distance object/background [mm]

1 = object black (6 % remission) , background white (90 % remission)

2 = object grey (18 % remission) , background white (90 % remission)

3 = object white (90 % remission) , background white (90 % remission)