

Technical Characteristics

Approvals	UL Listed, CSA Certified, CE Marked
Integrated Communications Ports	Modbus and CANopen
Ampere Rating	27.5A
Degree of Protection	IP20
EMC Filter	No Integrated EMC Filter (C2 EMC Filter available as option)
Horsepower Rating	7.5HP
Motor Power Rating	5.5kW
Operating Temperature	14°F to 122°F (-10°C to 50°C)
Input Voltage	208/240Vac
Marketing Trade Name	Altivar 312
Input Phase	3-Phase
Output Phase	3-Phase
Type	ATV312

Shipping and Ordering

Category	22152 -
Discount Schedule	CP4B
GTIN	00785901689355
Package Quantity	1
Weight	13.65 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	ID

[document.](#)