


FEATURES

- **Annealed Copper Conductor:** Provides superior electrical conductivity and durability
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors and ensures flexibility
- **Operating Temperature Range:** Suitable for environments from -15 °C to 90 °C
- **Voltage Rating of 500 V:** Ideal for medium voltage applications
- **4-Core Design:** Supports multiple connections and configurations
- **Plain Conductor Type:** Ensures easy installation and reliable performance
- **White Jacket Colour:** Facilitates easy identification and aesthetic integration
- **24/0.2 Core Strands:** Enhances flexibility and ease of handling

RS PRO 0.75 mm² Flexible Cable, 100 m

RS Stock No: 606-120



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for a wide range of industrial and commercial applications. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable's flexibility makes it ideal for installations where space is limited or where frequent movement is required.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	0.75 mm ²
Cable Length	100 m
Core Strands	24/0.2
Jacket Material	Polyvinyl Chloride
Number of Cores	4
Outside Diameter	8.3 mm

Operation Environment Specifications

Maximum Operating Temperature	90 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------