**ET·N** Cutler-Hammer

## Inductive Proximity Sensors iProx™

**iProx Inductive Proximity Sensors** 

## **Contents**

Model Selection, Compatible Connector Cables
Model Selection, Complementary and Dual Output 3-12
Model Selection, Accessories 3-13
Wiring Diagrams 3-14
Specifications 3-15 Dimensions 3-15

The Cutler-Hammer<sup>®</sup> iProx represents the highest performance, most versatile tubular inductive sensor offered by Eaton's electrical business. By utilizing an embedded microprocessor and exclusive SmartSense<sup>™</sup> technology, iProx can sense up to three times farther than typical sensors of its class, while providing an unheard-of level of customization.

Both shielded and unshielded versions of iProx feature extended sensing ranges. This allows the sensor to be mounted farther from the target, thereby reducing the potential for target impacts and increasing the sensing reliability of your application.

The iProx also includes a wide range of advanced features that can be enabled via optional programming tools. Using the ProxView Windows-based software package, an entirely custom sensor can be programmed to perfectly fit an application. Sensor characteristics, such as sensing range, can be customized down to the nearest tenth of a millimeter. Outputs can be changed from N.O. to N.C. Even noise immunity and response time can be adjusted if necessary. The iProx even features built-in timing delays and speed detection logic — no PLC programming is necessary.

With extended sensing range, quality construction and the ability to adapt to its environment, iProx is the ideal choice for even the most demanding inductive sensing applications.

## **Approvals**

C-UL Listed



Our Highest Performance, Most Versatile Inductive Sensor Yet

Vibration-Absorbing Potting Compound Dual Color, 360-Degree Output Indicator LED

Sense up to Three Times as Far as Conventional Sensors

Shock Absorbing Ryton® Face Cap Material

Note: Custom iProx models can also be ordered directly from the factory with pre-set ranges, outputs and connectors. Consult the Cutler-Hammer Application Engineers at 1-800-426-9184 for more information.

## **Product Features**

- Available in AC 2-Wire, DC 3-Wire and unique DC 4-Wire with complementary (N.O./N.C.) or dual N.O. outputs
- Reliably detect metal targets at up to three times the range of conventional shielded or unshielded tubular inductive sensors
- Quality construction using a stainless steel barrel, 360-degree dual-color LED indicator, Ryton<sup>®</sup> impact-resistant face cap and vibration-absorbing potting compound
- Auto-configure technology automatically detects a sinking (NPN) or sourcing (PNP) connection and switches the sensor accordingly, without any user intervention
- Exclusive SmartSense<sup>™</sup> embedded microprocessor technology allows for customizable range, band sensing, nuisance metal rejection, timing delays and over/under speed detection
- Optional computer programming cable and Windows-based ProxView configuration software makes it easy to customize sensors
- Withstands high electrical noise (up to 20 V/m)
- Resistant to extreme temperatures (-40°C)

# **Typical Applications**

- Automotive
- Machine Tool
- Material Handling
- Metalworking

**PROXIMITY SENSORS** 

m

# FIT-N (

# Inductive Proximity Sensors iProx™

	Operating Voltage	Sensing Range	Shielding	Connection Type <sup>②</sup>	Catalog Number	
					N.O. Output (1)	N.C. Output (1)
-Wire Sensors		•				
12 mm Diameter	6-48V DC	4 mm	Shielded	4-pin Micro DC Connector	E59-M12A105D01-D1 🕄	E59-M12A105D01-D2 🏵
Standard				4-pin Micro DC Pigtail ③	E59-M12A105D01P-D1 🏵	E59-M12A105D01P-D2 🏶
Range				2-meter Cable	E59-M12A105C02-D1	E59-M12A105C02-D2
Extended		10 mm	Unshielded	4-pin Micro DC Connector	E59-M12C110D01-D1 🏶	E59-M12C110D01-D2 🏵
Range				4-pin Micro DC Pigtail ③	E59-M12C110D01P-D1 🏵	E59-M12C110D01P-D2 🏵
				2-meter Cable	E59-M12C110C02-D1	E59-M12C110C02-D2
8 mm Diameter	-	8 mm	Shielded	4-pin Micro DC Connector	E59-M18A108D01-D1 🔅	E59-M18A108D01-D2 👀
Standard Range				4-pin Micro DC Pigtail <sup>3</sup>	E59-M18A108D01P-D1 🏵	E59-M18A108D01P-D2 🏵
				2-meter Cable	E59-M18A108C02-D1	E59-M18A108C02-D2
A Martine		18 mm	Unshielded	4-pin Micro DC Connector	E59-M18C116D01-D1 🏵	E59-M18C116D01-D2 🏵
Extended Range				4-pin Micro DC Pigtail <sup>3</sup>	E59-M18C116D01P-D1 🏵	E59-M18C116D01P-D2 🏵
				2-meter Cable	E59-M18C116C02-D1	E59-M18C116C02-D2
30 mm Diameter	-	15 mm	Shielded	4-pin Micro DC Connector	E59-M30A115D01-D1 🏵	E59-M30A115D01-D2 🕄
				4-pin Micro DC Pigtail ③	E59-M30A115D01P-D1 🌐	E59-M30A115D01P-D2 🕄
Standard Range				2-meter Cable	E59-M30A115C02-D1	E59-M30A115C02-D2
ATCH.		29 mm	Unshielded	4-pin Micro DC Connector	E59-M30C129D01-D1 🏵	E59-M30C129D01-D2 🏵
Extended Range				4-pin Micro DC Pigtail ③	E59-M30C129D01P-D1 🏵	E59-M30C129D01P-D2 🏵
				2-meter Cable	E59-M30C129C02-D1	E59-M30C129C02-D2

## Model Selection — iProx (Continued)

① Sensors are ordered with pre-set outputs from the factory, but can be later programmed either N.O. or N.C. using the ProxView software.

<sup>②</sup> For sensors with custom cable lengths or PUR jackets, contact Application Engineering at 1-800-426-9184.

<sup>③</sup> Standard pigtail cable length is 12 inches.

Fast turn product with typical one business day lead-time to shipment.

(a) See listing of compatible connector cables below.

### Model Selection — Compatible Connector Cables @

Voltage		Gauge	Length Catalog Number			log Number		Pin Configuration/Wire Colors	
Style	of Pins				PVC	Jacket	PUR Jacket	IRR PUR Jacket	(Face View Female Shown)
							·		
AC	3-pin 3-wire	22 AWG	6.0 fee	t (2m)	CSA	AS3F3CY2202	CSAS3F3RY2202	-	(2) (3) 1-Green 2-Red/Black 3-Red/White
DC	4-pin 4-wire	22 AWG	6.0 fee	t (2m)	CSE	DS4A4CY2202	CSDS4A4RY2202	CSDS4A4I02202	(1) (2) (4) (3) (4) (3) (4) (3) (4) (4) (4) (4) (4) (4) (4) (4) (4) (4)
Voltage Style						Length	Catalog Number	talog Number Pin Configuration/Wire Colors (Face View Female Shown)	
	_	3-pin		16 AWG		6 feet (2m)	CSMS3F3CY1602		2-Black 3-White
	Style AC	Style of Pins   AC 3-pin 3-wire   DC 4-pin 4-wire   Voltage	Style of Pins   AC 3-pin 3-wire 22 AWG   DC 4-pin 4-wire 22 AWG   Voltage Style Numbe of Pins	Style of Pins   AC 3-pin 3-wire 22 AWG   DC 4-pin 4-wire 22 AWG   6.0 fee   Voltage Number of Pins	Style of Pins o   AC 3-pin 3-wire 22 AWG 6.0 feet (2m)   DC 4-pin 4-wire 22 AWG 6.0 feet (2m)   Voltage Style Number of Pins Gauge	Style of Pins PVC   AC 3-pin 3-wire 22 AWG 6.0 feet (2m) CSA   DC 4-pin 4-wire 22 AWG 6.0 feet (2m) CSE   Voltage Number of Pins Gauge	Style of Pins Proc Jacket   AC 3-pin 3-wire 22 AWG 6.0 feet (2m) CSAS3F3CY2202   DC 4-pin 4-wire 22 AWG 6.0 feet (2m) CSDS4A4CY2202   Voltage Number of Pins Gauge Length	Style of Pins O PVC Jacket PUR Jacket   AC 3-pin 3-wire 22 AWG 6.0 feet (2m) CSAS3F3CY2202 CSAS3F3RY2202   DC 4-pin 4-wire 22 AWG 6.0 feet (2m) CSDS4A4CY2202 CSDS4A4RY2202   Voltage Style Number of Pins Gauge Length Catalog Number	Style of Pins PVC Jacket PUR Jacket IRR PUR Jacket   AC 3-pin 3-wire 22 AWG 6.0 feet (2m) CSAS3F3CY2202 CSAS3F3RY2202    DC 4-pin 4-wire 22 AWG 6.0 feet (2m) CSDS4A4CY2202 CSDS4A4RY2202 CSDS4A4I02202   Voltage Number of Pins Gauge Length Catalog Number Pin Configuration/V (Face View Female    3-pin 16 AWG 6 feet (2m) CSMS3F3CY1602

 ${}^{\textcircled{4}}$  For a full selection of connector cables, see Section 10.

Stocked product, typical order quantities guaranteed in stock.

c

# **E·T**•**N** Cutler-Hammer

# Inductive Proximity Sensors iProx™

### Specifications — iProx

•									
Description	2-Wire Sensors	3-Wire Sense	ors						
Input Voltage	20 – 132V AC 6 – 48V DC								
Load Current	12 mm: 5 – 300mA, 200mA > 50°C	≤500 mA @ 6 – 30V DC; ≤300 mA @ 32 – 48V DC							
Leakage Current	≤1.7 mA @ 0°C, 2.0 mA @ -40°C	≤150 µA	≤150 μA						
Voltage Drop	<5V AC	≤2.5V DC	≤2.5V DC						
Burden Current	—	≤15 mA							
Protection	None	Auto Reset							
Switching Hysteresis	< 15% Rated Sensing Distance								
Repeat Accuracy	Shielded models: < 1% Sensing Distance; Unshielded models: < 3% Sensing Distance								
Surge Capacity	3A/30 ms	_							
Temperature Range	-40° to 158°F (-40° to 70°C)								
Material of Construction	303 Stainless steel; End bells: Polycarbonate; Face caps: Ryton <sup>®</sup> ; Cable: AWM Style 20387 (PVC) ③								
Vibration and Shock	Vibration: 10 to 55 Hz, 1 mm Amplitude, IEC 60068-2-6; Shock: 30g, 11 mS per IEC 68-2-27								
Indicator LED	360° viewable LED								
Enclosure Ratings	NEMA 4, 4X, 6, 6P, 12 and 13 (IP67) ④								
Response Time ①	2-Wire Sensors 3-Wire Sensors								
	All 2-Wire Models	Shielded	Shielded			Unshielded			
		12 mm	18 mm	30 mm	12 mm	18 mm	30 mm		
Factory Default Mode	Shipped in "Side by Side Mode" by default (20 V/m)	580 Hz (10 V/m)	390 Hz (10 V/m)	240 Hz (10 V/m)	300 Hz (10 V/m)	150 Hz (10 V/m)	145 Hz (10 V/m)		
Side by Side <sup>②</sup>	30 Hz (10 V/m)	50 Hz (20 V/	50 Hz (20 V/m)						
High Noise Immunity Mode	10 Hz (>20 V/m)	10 Hz (>20 V	10 Hz (>20 V/m)						

 iProx sensors may be programmed to perform in Side by Side or High Noise immunity applications using the iProx Programming Cable (E59RP1) & ProxView software (E59SW1).


② Use the Side by Side response time parameter when using the iProx Tray Programmer (E59TP1), iProx Programming Cable (E59RP1) and ProxView software (E59SW1).

<sup>③</sup> Ryton<sup>®</sup> is a registered trademark of Phillips Chemical (division of Phillips Petroleum).

<sup>④</sup> Our products conform to NEMA tests as indicated, however, some severe washdown applications can exceed these NEMA test specifications. For questions about a specific application, contact our applications department at 1-800-426-9184.

### Approximate Dimensions — iProx in Inches (mm)


#### **Cable Models**



## **Cable Models**

Size	Shielding	Α	В	C	D
12 mm	Shielded	2.46 (62.4)	1.98 (50.3)	0.02 (0.5)	0.67 (17)
	Unshielded	2.46 (62.4)	1.64 (41.6)	0.36 (9)	0.67 (17)
18 mm	Shielded	2.54 (64.5)	2.00 (50.9)	0.02 (0.5)	0.94 (24)
	Unshielded	2.54 (64.5)	1.47 (37.4)	0.55 (14)	0.94 (24)
30 mm	Shielded	2.74 (69.6)	2.13 (54.1)	0.03 (0.75)	1.41 (36)
	Unshielded	2.74 (69.6)	1.41 (35.8)	0.75 (19)	1.41 (36)

### **Micro-Connector Models**



### **Micro-Connector Models**

Size	Shielding	Α	В	C	D
12 mm	Shielded	2.71 (68.7)	1.98 (50.3)	0.02 (0.5)	0.67 (17)
	Unshielded	2.71 (68.7)	1.64 (41.6)	0.36 (9)	0.67 (17)
18 mm	Shielded	2.73 (69.3)	2.00 (50.9)	0.02 (0.5)	0.94 (24)
	Unshielded	2.73 (69.3)	1.47 (37.4)	0.55 (14)	0.94 (24)
30 mm	Shielded	2.92 (74.1)	2.13 (54.1)	0.03 (0.75)	1.41 (36)
	Unshielded	2.92 (74.1)	1.41 (35.8)	0.75 (19)	1.41 (36)