

# Sapphire Nano Foam

## Ultra-thin cut resistant glove with nitrile foam coating

As the thinnest option available on the market with a high cut resistance (level D), Sapphire Nano Foam offers an outstanding level of tactility to perform extreme precision tasks. With a nitrile foam coated palm, the second skin feeling has never been better to work in oily and wet conditions.

### Features

- ▲ Medium to high cut resistance: Level D/ ANSI A4
- ▲ 21 gauge seamless liner offers unprecedented level of fingertip sensitivity for precision tasks
- ▲ Durable nitrile foam palm coating ensures good protection against oily and wet parts
- ▲ Reinforced thumb crotch enhances durability
- ▲ Touchscreen capabilities to allow usage with screen devices
- ▲ Designed for easy movement and continuous wear
- ▲ Breathable back of hand to reduce perspiration
- ▲ Seamless knit prevents irritation



### Certifications



### Suitable industries & applications

#### Industries

- ▲ Automotive
- ▲ Construction
- ▲ Manufacturing
- ▲ Facilities Management

- ▲ Utilities
- ▲ Highways and Infrastructure

#### Applications

- ▲ Machinery and Plant Operation
- ▲ Component and Product Assembly
- ▲ Vehicle Repairs and Maintenance
- ▲ Handling Sharp or Abrasive Materials

#### Europe

sales@globus.com  
+44 (0)161 877 4747  
+44 (0)161 877 4746

#### Middle East & Africa

sales.gcc@globusgroup.com  
+971 4 882 9962  
+971 4 882 9963

#### Americas

salesusa@globusgroup.com  
+1 83 337 54747

# Sapphire Nano Foam

Ultra-thin cut resistant glove with nitrile foam coating

## Product information

<b>Materials</b>	Liner:	21 Gauge Engineered HPPE, Nylon, Steel, HPPE
	Coating:	Foam Nitrile
<b>Colour</b>	Grey / Black	
<b>Length</b>	220mm	
<b>Cuff Style</b>	Elasticated Knit Wrist	

## Ordering information

<b>XS</b>	SKG00050BB	Items per Pack 10 x Pairs
<b>S</b>	SKG00050BD	
<b>M</b>	SKG00050BF	Items per Case 120 x Pairs
<b>L</b>	SKG00050BH	
<b>XL</b>	SKG00050BJ	
<b>XXL</b>	SKG00050BL	
<b>XXXL</b>	SKG00050BN	

## Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

### Europe

sales@globus.com  
+44 (0)161 877 4747  
+44 (0)161 877 4746

### Middle East & Africa

sales.gcc@globusgroup.com  
+971 4 882 9962  
+971 4 882 9963

### Americas

salesusa@globusgroup.com  
+1 83 337 54747

**Globus Group**, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM  
**Globus EMEA FZE**, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES  
**Globus Americas LLC**, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.  
The manufacturer reserves the right to make any modifications it deems necessary.