



**SAFETY DATA SHEET**  
SAFE STEP 50 - ALL COLOURS

Page: 1

Compilation date: 15/05/2015

Revision date: 16/01/2019

Revision No: 3

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** SAFE STEP 50 - ALL COLOURS

**Product code:** 43070, 43071

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** Anti-slip Floor Paint for roller application.

**1.3. Details of the supplier of the safety data sheet**

**Company name:** ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

**Tel:** +44 (0) 113 232 2700

**Fax:** +44 (0) 113 232 2740

**Email:** [customer-service@rocol.com](mailto:customer-service@rocol.com)

**1.4. Emergency telephone number**

**Emergency tel:** +44 (0) 113 232 2600

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** Aquatic Chronic 3: H412; Flam. Liq. 3: H226

**Most important adverse effects:** Flammable liquid and vapour. Harmful to aquatic life with long lasting effects.

**2.2. Label elements**

**Label elements:**

**Hazard statements:** H226: Flammable liquid and vapour.

H412: Harmful to aquatic life with long lasting effects.

**Hazard pictograms:** GHS02: Flame



**Signal words:** Warning

**Precautionary statements:** P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition

[cont...]

# SAFETY DATA SHEET

## SAFE STEP 50 - ALL COLOURS

Page: 2

sources. No smoking.

P240: Ground and bond container and receiving equipment.

P241: Use explosion-proof electrical/ventilating/lighting/... equipment.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P303+P361+P353: IF ON SKIN (or hair): Take off immediately all contaminated clothing.

Rinse skin with water .

P370+P378: In case of fire: Use media other than water to extinguish.

### 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

HYDROCARBONS, C9, AROMATICS - REACH registered number(s): 01-2119455851-35-XXXX

EINECS	CAS	PBT / WEL	CLP Classification	Percent
918-668-5	-	-	Flam. Liq. 3: H226; STOT SE 3: H335; Asp. Tox. 1: H304; Aquatic Chronic 2: H411; STOT SE 3: H336; -: EUH066	10-20%

1-METHOXY-2-PROPANOL - REACH registered number(s): 01-2119457435-35-XXXX

203-539-1	107-98-2	-	Flam. Liq. 3: H226; STOT SE 3: H336	1.0-10%
-----------	----------	---	-------------------------------------	---------

XYLENE - REACH registered number(s): 01-2119488216-32-XXXX

215-535-7	1330-20-7	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Skin Irrit. 2: H315	1.0-10%
-----------	-----------	---	---	---------

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water. Remove all contaminated clothes and footwear immediately unless stuck to skin. Obtain medical attention if soreness or redness persists.

**Eye contact:** Bathe the eye with running water for 15 minutes. Obtain medical attention if soreness or redness persists.

**Ingestion:** Wash out mouth with water. Seek medical attention if you feel unwell.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Seek medical attention if you feel unwell.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be irritation of the throat.

[cont...]

**SAFETY DATA SHEET**  
SAFE STEP 50 - ALL COLOURS

Page: 3

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest.

**Delayed / immediate effects:** No data available.

**4.3. Indication of any immediate medical attention and special treatment needed**

**Immediate / special treatment:** No data available.

**Section 5: Fire-fighting measures**

**5.1. Extinguishing media**

**Extinguishing media:** Water spray. Carbon dioxide. Dry chemical powder.

**5.2. Special hazards arising from the substance or mixture**

**Exposure hazards:** Flammable. In combustion emits toxic fumes.

**5.3. Advice for fire-fighters**

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

**Section 6: Accidental release measures**

**6.1. Personal precautions, protective equipment and emergency procedures**

**Personal precautions:** Refer to section 8 of SDS for personal protection details. Eliminate all sources of ignition. Turn leaking containers leak-side up to prevent the escape of liquid.

**6.2. Environmental precautions**

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

**6.3. Methods and material for containment and cleaning up**

**Clean-up procedures:** Mix with sand or vermiculite. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

**6.4. Reference to other sections**

**Reference to other sections:** Refer to section 8 of SDS. Refer to section 13 of SDS.

**Section 7: Handling and storage**

**7.1. Precautions for safe handling**

**Handling requirements:** Smoking is forbidden. Ensure there is sufficient ventilation of the area.

**7.2. Conditions for safe storage, including any incompatibilities**

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition.

**Suitable packaging:** Must only be kept in original packaging.

**7.3. Specific end use(s)**

**Specific end use(s):** No data available.

[cont...]

**SAFETY DATA SHEET**  
SAFE STEP 50 - ALL COLOURS

Page: 4

**Section 8: Exposure controls/personal protection**

**8.1. Control parameters**

**Hazardous ingredients:**

**HYDROCARBONS, C9, AROMATICS**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
EU	100mg/m <sup>3</sup>	-	-	-

**1-METHOXY-2-PROPANOL**

UK	375 mg/m <sup>3</sup>	560 mg/m <sup>3</sup>	-	-
----	-----------------------	-----------------------	---	---

**XYLENE**

UK	220 mg/m <sup>3</sup>	441 mg/m <sup>3</sup>	-	-
----	-----------------------	-----------------------	---	---

**DNEL/PNEC Values**

**Hazardous ingredients:**

**HYDROCARBONS, C9, AROMATICS**

Type	Exposure	Value	Population	Effect
DNEL	Dermal (repeated dose)	25	Workers	Systemic
DNEL	Inhalation (repeated dose)	150	Workers	Systemic
DNEL	Dermal (repeated dose)	11	Consumers	Systemic
DNEL	Inhalation (repeated dose)	32	Consumers	Systemic

**XYLENE**

Type	Exposure	Value	Population	Effect
DNEL	Inhalation	289	Workers	Systemic
DNEL	Dermal	180	Workers	Systemic
DNEL	Inhalation (repeated dose)	77	Workers	Systemic
DNEL	Inhalation (repeated dose)	174	Consumers	Systemic
DNEL	Inhalation (repeated dose)	174	Consumers	Local
DNEL	Dermal	108	Consumers	Local
DNEL	Inhalation	14.8	Consumers	Local
PNEC	Fresh water	0.327	-	-
PNEC	Marine water	0.327	-	-
PNEC	Microorganisms in sewage treatment	6.58	-	-
PNEC	Fresh water sediments	12.46	-	-
PNEC	Marine sediments	12.46	-	-

[cont...]

**SAFETY DATA SHEET**  
SAFE STEP 50 - ALL COLOURS

Page: 5

PNEC	Soil (agricultural)	2.31	-	-
------	---------------------	------	---	---

**8.2. Exposure controls**

**Engineering measures:** Ensure there is sufficient ventilation of the area.

**Respiratory protection:** Gas/vapour filter, type A: organic vapours (EN141).

**Hand protection:** Gloves (solvent-resistant).

**Eye protection:** Safety glasses with side-shields. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

**Environmental:** No special requirement.

**Section 9: Physical and chemical properties**

**9.1. Information on basic physical and chemical properties**

**State:** Liquid

**Colour:** Various

**Odour:** Characteristic odour

**Evaporation rate:** Fast

**Oxidising:** No data available.

**Solubility in water:** Insoluble

**Viscosity:** Viscous

**Boiling point/range°C:** No data available.

**Melting point/range°C:** No data available.

**Flammability limits %: lower:** No data available.

**upper:** No data available.

**Flash point°C:** 25

**Part.coeff. n-octanol/water:** No data available.

**Autoflammability°C:** Not applicable.

**Vapour pressure:** No data available.

**Relative density:** 1.37-1.50

**pH:** No data available.

**VOC g/l:** 465

**9.2. Other information**

**Other information:** Not applicable.

**Section 10: Stability and reactivity**

**10.1. Reactivity**

**Reactivity:** Stable under recommended transport or storage conditions.

**10.2. Chemical stability**

**Chemical stability:** Stable under normal conditions.

**10.3. Possibility of hazardous reactions**

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.

**10.4. Conditions to avoid**

**Conditions to avoid:** Heat. Hot surfaces. Sources of ignition. Flames.

[cont...]

**SAFETY DATA SHEET**  
SAFE STEP 50 - ALL COLOURS

Page: 6

**10.5. Incompatible materials**

**Materials to avoid:** Strong oxidising agents. Strong acids.

**10.6. Hazardous decomposition products**

**Haz. decomp. products:** In combustion emits toxic fumes.

**Section 11: Toxicological information**

**11.1. Information on toxicological effects**

**Hazardous ingredients:**

**1-METHOXY-2-PROPANOL**

IVN	RAT	LD50	4200	mg/kg
ORL	MUS	LD50	11700	mg/kg
ORL	RAT	LDLO	3739	mg/kg

**XYLENE**

ORL	MUS	LD50	2119	mg/kg
ORL	RAT	LD50	4300	mg/kg
SCU	RAT	LD50	1700	mg/kg

**Toxicity values:** No data available.

**Symptoms / routes of exposure**

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be irritation of the throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest.

**Delayed / immediate effects:** No data available.

**Other information:** Not applicable.

**Section 12: Ecological information**

**12.1. Toxicity**

**Hazardous ingredients:**

**HYDROCARBONS, C9, AROMATICS**

Daphnia magna	48H EC50	3.2	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	9.2	mg/l

**12.2. Persistence and degradability**

**Persistence and degradability:** No data available.

[cont...]

**SAFETY DATA SHEET**  
SAFE STEP 50 - ALL COLOURS

Page: 7

**12.3. Bioaccumulative potential**

**Bioaccumulative potential:** No data available.

**12.4. Mobility in soil**

**Mobility:** Readily absorbed into soil.

**12.5. Results of PBT and vPvB assessment**

**PBT identification:** This product is not identified as a PBT/vPvB substance.

**12.6. Other adverse effects**

**Other adverse effects:** Harmful to aquatic organisms.

**Section 13: Disposal considerations**

**13.1. Waste treatment methods**

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**Recovery operations:** Solvent reclamation/regeneration.

**Waste code number:** 08 01 11

**Disposal of packaging:** Dispose of as normal industrial waste.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

**Section 14: Transport information**

**14.1. UN number**

**UN number:** UN1263

**14.2. UN proper shipping name**

**Shipping name:** PAINT RELATED MATERIAL

**14.3. Transport hazard class(es)**

**Transport class:** 3

**14.4. Packing group**

**Packing group:** III

**14.5. Environmental hazards**

**Environmentally hazardous:** No

**Marine pollutant:** No

**14.6. Special precautions for user**

**Special precautions:** No special precautions.

**Tunnel code:** D/E

**Transport category:** 3

[cont...]

**SAFETY DATA SHEET**  
SAFE STEP 50 - ALL COLOURS

Page: 8

**Section 15: Regulatory information**

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

**15.2. Chemical Safety Assessment**

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

**Section 16: Other information**

**Other information**

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

Compiled in accordance with REACH.

**Phrases used in s.2 and s.3:** EUH066: Repeated exposure may cause skin dryness or cracking.

H226: Flammable liquid and vapour.

H304: May be fatal if swallowed and enters airways.

H312: Harmful in contact with skin.

H315: Causes skin irritation.

H332: Harmful if inhaled.

H335: May cause respiratory irritation.

H336: May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.