


# AC2910



## AS-Interface ProcessLine module

ProcessLine 8DI IP69K



Application	
Application	hygienic and wet areas in the food industry
Electrical data	
Operating voltage [V]	26.5...31.6 DC
Max. current consumption from AS-i [mA]	500
Inputs / outputs	
Number of inputs and outputs	Number of digital inputs: 8
Inputs	
Number of digital inputs	8; (2 x Slave)
Input circuit of digital inputs	PNP; (type 2 according to IEC 61131-2)
Sensor supply of the inputs	AS-i
Power supply [V]	18...30; (DC)
Max. total current rating of inputs [mA]	400
Input current High [mA]	6...10
Input current Low [mA]	0...2
Switching level high [V]	> 11
Digital inputs protected against short circuits	yes
Operating conditions	
Ambient temperature [°C]	-5...70
Max. relative air humidity [%]	90; (linearly decreasing to 50 % (40 °C) non condensing)
Max. height above sea level [m]	2000
Protection	IP 68; IP 69K
Pollution degree	2
Tests / approvals	
EMC	EN 62026-2 EN 61000-6-2

# AC2910



## AS-Interface ProcessLine module

ProcessLine 8DI IP69K


MTTF	[years]	212			
<b>AS-i classification</b>					
AS-i version		2.1			
Extended addressing mode		yes			
AS-i master profile		M2; M3; M4			
AS-i profile		S-0.A.E			
AS-i I/O configuration	[hex]	0			
AS-i ID code	[hex]	A.E			
AS-i certificate		88901			
Assignment of the data bits	data bit	D0	D1	D2	D3
	input	1	2	3	4
	socket	I-1/2	I-1/2 I-2	I-3/4	I-3/4 I-4
	pin	4	2 4	4	2 4
<b>Mechanical data</b>					
Weight	[g]	644			
Dimensions	[mm]	Ø 137.3 / L = 80			
Materials		threaded bush: stainless steel (316L/1.4404); LED-Fenster: PC; O-ring: EPDM; Protective cap: PP			
<b>Displays / operating elements</b>					
Display	operation	LED, green			
	errors	LED, red			
	function	LED, yellow			
<b>Electrical connection</b>					
Module connection		M12			
<b>Accessories</b>					
Items supplied		Protective cap: M12, E70297			
Accessories (optional)		Torque wrench:, E70390			
		Flat cable insulation displacement connector:, E70454			
<b>Remarks</b>					
Remarks		Inputs and outputs must be electrically isolated.			
		Do not connect any of the following points to an external potential:			
		I-, I+, I-1/2, I-2, I-3/4, I-4			
		The connections are electrically connected with the AS-i cable.			
		default setting of the ID1 codes: slave 1=1 / slave 2=2			
Pack quantity		The round cable connected to AS-i should not be longer than 2 m.			
		1 pcs.			

## AS-Interface ProcessLine module

ProcessLine 8DI IP69K

### Electrical connection - AS-i


Connector: M12; coding: A; Tightening torque: 1.2...1.4 Nm




1	AS-i+
2	n.c.
3	AS-i -
4	n.c.
5	functional earth FE

### Electrical connection - Inputs

Connection



Connector: M12; coding: A; Tightening torque: 1.2...1.4 Nm



1	Sensor supply L+
3	Sensor supply L-
5	functional earth