



Product: [10GB24C](#)

10GB Category 6A Enhanced Cable, 4 Pair, U/UTP, LSZH Indoor CPR Cca

Product Description
Category 6A Premise Horizontal Cable (625MHz), 4-Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Polyethylene Insulation, LSZH Jacket

Technical Specifications

Product Overview

Suitable Applications:	Horizontal and building backbone cable; Support current and future Category 6A and 6 applications, such as: 10GBase-T (10 Gigabit Ethernet), 1000Base-T (Gigabit Ethernet), 100 Base-T, 10 Base-T, FDDI, ATM
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
23 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene	1.2 mm (0.047 in)	White / Blue & Blue, White / Orange & Orange, White / Green & Green, White / Brown & Brown

Cable Core

Description	Separator
4 pairs twisted to cable core covered with a polyester foil	Center Member (Patented X-Spline®), EquiBlock™ Barrier Technology

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	7.6 mm (0.30 in)

Overall Cable Diameter (Nominal):	7.6 mm (0.30 in)
-----------------------------------	------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Mutual Capacitance	Max. Capacitance Unbalance	Nom. Characteristic Impedance
95 Ohm/km	56 pF/m (17 pF/ft)	160 pF/100m	100 Ohm

Delay

Max. Delay Skew	Nom. Velocity of Prop.
45 ns/100m	67%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. PSANEXT [dB]	Min. PSAACRF [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
1	2.1 dB/100m	75.3	72.3	73.2	70.2	68	65.0	20	67.0	67	40	35
4	3.8 dB/100m	66.3	63.3	62.5	59.5	56	53.0	23	67.0	66.2	40	23
10	5.9 dB/100m	60.3	57.3	54.4	51.4	48	45.0	25	67.0	58.2	40	15
16	7.5 dB/100m	57.2	54.2	49.8	46.8	43.9	40.9	25	67.0	54.1	38	10.9

31.2	10.5 dB/100m	52.9	49.9	42.4	39.4	38.1	35.1	23.6	67.0	48.3	35.1	5.1
62.5	15 dB/100m	48.4	45.4	33.4	30.4	32.1	29.1	21.5	65.6	42.3	32	
100	19.1 dB/100m	45.3	42.3	26.2	23.2	28	25.0	20.1	62.5	38.2	30	
125	21.5 dB/100m	43.8	40.8	22.3	19.3	26.1	23.1	19.4	61.0	36.3	29	
200	27.6 dB/100m	40.8	37.8	13.2	10.2	22	19.0	18	58.0	32.2	27	
250	31.1 dB/100m	39.3	36.3	8.3	5.3	20	17.0	17.3	56.5	30.2	26	
300	34.3 dB/100m	38.1	35.1	3.9	0.9	18.5	15.5	17.3	55.3	28.7		
500	45.3 dB/100m	34.8	31.8	-10.4	-13.4	14	11.0	17.3	52.0	24.2		
625	51.2 dB/100m	33.4	30.4	-17.8	-20.8	12.1	9.1	14.5	50.6	22.3		

Voltage

Voltage Rating
72 V DC

Mechanical Characteristics

Temperature

Operating	Installation
-30°C to 60°C	0°C To +50°C

Bend Radius

Stationary Min.	Installation Min.
31 mm (1.2 in)	62 mm

Max. Pull Tension:	110 N (25 lbf)
Bulk Cable Weight:	59 kg/km

Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Cca
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Cca-s1a,d1,a1; CPR UKCA Class: Cca-s1a,d1,a1
IEEE Compliance:	PoE: IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Data Category:	Category 6A
TIA/EIA Compliance:	ANSI/TIA 568.2-D
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61034-2 - Smoke Density Min Transmittance = 80%
CENELEC Compliance:	EN 50173-1, Segregation class according EN50174-2 = b
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system.
--------	--

History

Update and Revision:	Revision Number: 0.191 Revision Date: 01-13-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
10GB24C.06500	Blue	Reel	500 m	8719605160225
10GB24C.05500	Green	Reel	500 m	8719605227546
10GB24C.07500	Purple	reel	500 m	8719605233127
10GB24C.09500	White	Reel	500 m	8719605180261

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.