

EDS 2000 S

Dial torque wrench

0.8 - 2000 Nm / 7 lbf·in - 1500 lbf·ft / with signal

Code **1196804** ETIM **EC002132**

EAN **4002805918166** UNSPSC **27-11-17-15**

Country of origin **Germany** eCl@ss **21-04-02-22**

Customs tariff number
82041100



Article description

- Use:
- Controlled tightening and verification of tightening values
- For use in almost all industrial manufacturing areas
- Working ranges from 0.8 - 2000 Nm / 7 lbf·in - 1500 lbf·ft are covered
- Features:
- Dial-indicating torque wrench with dual scale and slave pointer
- 1/4", 3/8", 1/2", 3/4" or 1" double square drive with ball lock for controlled right and left tightening
- Models No. ADS 4 to No. ADS 40: With integrated ratchet function
- For controlled screw tightening and torque measurements
- Display accuracy: +/- 4 % tolerance of the indicated value
- Acc. to DIN EN ISO 6789, traceable to national standards
- With dual scale in Nm and lbf·in or lbf·ft double-tinted clearly readable face
- Built-in overload protection – mechanical stop up to a maximum of 25% overload of the maximum value
- Housing made of light, robust special aluminium construction - painted silver-grey
- Black, non-slip rubber handgrips
- Model No. ADS 4 to No. ADS 40: EPA (Electrostatic Protected Area) compliant, for use in electrostatically sensitive applications
- With audio-visual signal
- Test certificate acc. to DIN EN ISO 6789

Article information

Contents [Qty of pieces]	1	Torque [max.] [lbf·ft]	1500 lbf·ft
Net weight [kg]	16,7 kg	Torque range [min./max.] [N·m]	400 Nm - 2000 Nm
Total length [mm]	2.040 mm	Torque range [min./max.] [lbf·ft]	300 lbf·ft - 1500 lbf·ft
Total height [mm]	138 mm	Graphic display	no
Drive connector square (male)	1"	Epa-/Esd-Model	no
Drive connector square (male)	25 mm	Fixed setting	no
Drive type/drive	Double square	Graduation	50
Torque [min.] [N·m]	400 Nm	Graduation [lbf·ft]	50 lbf·ft
Torque [max.] [N·m]	2000 Nm	Graduation [n:m]	50 Nm
Torque [min.] [lbf·ft]	300 lbf·ft	Evaluation software	no