



Relay Catalog

- Facts & Figures
- News & More
- Automotive
- Modules/Relays
- Telecom/Signal Rel.
- Power Relays
- Relay Catalog
- Relay Lexicon



Components
with
system
vision



Miniature Relay PT


Ordering Designation: PT - 370 - 615
Dimensions (L x W x H): 28 mm x 22.5 mm x 29 mm

Features	Typical Applications
<ul style="list-style-type: none">2, 3 or 4 C/O contactsCadmium-free contact materialManual test tab, optionally lockableMechanical indicatorRelay height 29 mmSwitching performance up to 3000 VAWhite marking tabs	<ul style="list-style-type: none">Universal use in control and autom:

Design	
Terminal Design:	Solder/plug-in terminals
Case Sealing:	Dust protected
Version:	Standard, AMP 2.8; with test button

Dimensions (max.)	
Length:	28 mm
Width:	22.5 mm
Height:	29 mm
Weight:	30 g
Dimensional Drawing:	<p>The dimensional drawing illustrates the component's geometry from three perspectives: top, side, and bottom views. The top view shows a rectangular component with a width of 28 mm and a height of 29 mm. The side view shows a width of 22.5 mm and a height of 29 mm. The bottom view shows four pins with a pitch of 6.0 mm and a pin width of 0.5 mm. The side view also shows a pin height of 2.4 mm and a pin pitch of 1.2 mm. The bottom view shows a pin pitch of 2.2 mm. The side view shows a pin pitch of 1.2 mm and a pin pitch of 2.2 mm.</p>

All values valid at reference temp.:	20 °C
--------------------------------------	-------

Contact side	
Contact Configuration (number and type)	
Changeover:	3
Contact type :	
Single contact	Yes
Pin assignment:	
Rated current:	Break: 10 A, Make: 10 A
Make current max.:	Off: 20 A, On: 20 A
Break current max.:	Off: 10 A, On: 10 A
Limiting cont. current at ref. temp.:	Break: 10 A, Make: 10 A
Switching voltage :	
Max. AC:	440 V
Switching power (see load limit curve)	
Contact material:	AgNi 90/10
Note:	Approvals on request

Energizing Side	
Switching behavior:	monostabil
Actuating system:	AC
Magnet system:	Nonpolarized
Number of coils:	1
Nominal voltage:	115 V
Coil resistance at ref. temp. 20 °C:	4845 Ohm +/- 581.4 Ohm
Nominal power at ref. temp.:	1 VA
Operating voltage range	
Must operate voltage (Minimum voltage without pre-energizing):	92 V
Min. release voltage:	34.5 V
Switching times	
Operate time at nominal voltage, typ.:	15 ms
Release time typ	
without coil suppression:	10 ms
Bounce time typ.	
Break contact:	5 ms
Make contact:	5 ms

Insulation	
Tracking resistance of the base acc. to IEC 112:	CTI 175
Insulation by IEC 664/VDE 110 (1/89)	
Rated voltage:	250 V
Pollution degree:	3
Overvoltage category:	III
Nominal voltage VDE 110 (2/79)	
Insulation Group B:	250 V
Insulation Group C:	250 V
Dielectric test voltage AC	
Contact/Coil:	2.5 kV
Between neighbouring contacts:	2.5 kV
At open contact:	1.5 kV

General data	
Permissible ambient temp. in operation:	Min. -45 °C , Max. 70 °C
Mechanical endurance:	20000000 switching cycles
Flammability to UL:	V-0
Electrical endurance (Graphic):	

Operating conditions	
Vibration resistance:	NO: >7 * 9,81m/s ² ; NC: >4 * 9,81m/s ²
Shock resistance:	NO: >20*9,81 m/s ² ; NC: >5*9,81 m/s ²

Your local Siemens partner will be pleased to inform you about ordering details.

How are we doing? Tell us about your impression and ideas for this new Relay Catalog.

Just click on the icon that best represents your opinion:

