Max. 54 m³/h

AC centrifugal fans

□ 135 x 38 mm

Material:

Scroll housing: GRP1) (PBT)

Impeller: GRP1) (PA)

Housing base: Sheet steel

Direction of air flow: Centrifugal: discharge through

window in housing

Direction of rotation: Clockwise,

looking towards rotor

Connection: To 2 single wires AWG 22.

Highlights: Forward-curved impeller

Weight: 560 g - Possible special versions:


(See page 10)

- Moisture protection
- Salt spray protection

- Degree of protection: IP 54

1) Fiberglass-reinforced plastic

Series RG 90 VHS0090XQHCS Nominal data	Air flow	Air flow	Nominal voltage	Frequency	Sound power level	Cinton closus howing	Ball bearings	Power consumption	Nominal speed	Temperature range	Service life L ₁₀ at 40 °C at T _{max}	Curve
Туре	m³/h	cfm	VAC	Hz	Bel(A)		/ =	Watts	rpm⁻¹	°C	Hours Hours	
RG 90-18/50	54	32	230	50	5.8			22.0	2 200	-30+60	35 000 / 22 500	1
RG 90-18/56	54	32	230	50	5.8		•	22.0	2 200	-30+60	35 000 / 22 500	1
RG 90-18/00	47	28	115	60	6.2		1	22.0	1 900	-30+65	35 000 / 20 000	2
RG 90-18/06	47	28	115	60	6.2			22.0	1 900	-30+65	35 000 / 20 000	2
Subject to change												



Air performance measured according to: ISO 5801. Installation category A, without contact protection. Noise: Total sound power level L_WA ISO 10302 measured on a hemisphere with a radius of 2 m.

from fan axis.

The values given are applicable only under the specified measuring conditions and may differ depending on the installation conditions.

In the event of deviation from the standard configuration,

the parameters must be checked after installation For detailed information see

http://www.ebmpapst.com/general conditions

