



CUT PROTECTION


SKYTEC® | TRC705

A LIGHTWEIGHT PU COATED GLOVE WITH STEEL FIBRE AND RECYCLED POLYESTER

Outstanding cut resistance allowing protection in the most risky applications. PU coating protects the hand from abrasion and grease, delivering effective long lasting grip.

FEATURES

- › Cut resistant: Level E (EN 388:2016)
- › A flexible and comfortable glove offering great dexterity
- › HPPE on the inside provides comfort and protection
- › Fully encapsulated steel and nylon on the outside strengthens the protection against burrs and sharp edges
- › PU coating gives exceptional abrasion resistance and sensitivity allowing workers to handle small pieces
- › Reinforced thumb crotch enhances durability
- › RCS (Recycled claim Standard) certified
- › 1 pair = 1 PET bottle of 500ml recycled
- › Seamless knit prevents irritation
- › Designed for easy movement and continuous wear



SUITABLE FOR

Typical Industries

- Automotive
- Construction
- Logistics
- Maintenance
- Manufacturing
- Metal Industry

Suitable Applications

- Assembly
- Handling sharp and greasy parts
- Machining
- Bodywork
- Precision mechanics
- Metal stamping

CERTIFICATION



See overleaf for explanation



SKYTEC® TRC705

PRODUCT INFORMATION

MATERIALS	LINER:	13 gauge HPPE, steel fibre, recycled polyester
	COATING:	Polyurethane (PU)
COLOUR	Green/black	
LENGTH (mm)	250 (Size Dependent)	
CUFF STYLE	Elasticated knit wrist	

RECOMMENDATIONS FOR USE

- **USE:** General handling glove with cut protection. Not suitable for thermal, electrical, chemical protection. Do not use near moving machines if there is a risk of entanglement
- **STORAGE:** Store in dry conditions in the original packaging and away from direct sunlight
- **CLEANING:** To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present
- **LIFETIME:** Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use

ORDERING DETAILS

SIZE	CODE	PACKAGING
6/XS	SKG00015EB	10 pairs per bag 120 pairs per case
7/S	SKG00015ED	
8/M	SKG00015EF	
9/L	SKG00015EH	
10/XL	SKG00015EJ	
11/XXL	SKG00015EL	

CERTIFICATION LEGENDS



MECHANICAL HAZARDS EN 388:2016 PERFORMANCE LEVELS*

0-4	0-5	0-4	0-4	A-F	P
Abrasion Resistance		Circular Blade Cut Resistance		Impact Resistance	
		Tear Resistance		Straight Blade Cut Resistance (EN ISO: 13997)	
				Puncture Resistance	

*If tests are not performed or are not applicable, 'X' will be placed instead of a number/letter

CLASSIFICATION FOR CUT RESISTANCE

Measured breakthrough time	Permeation performance index (grams)
A1	≥ 200
A2	≥ 500
A3	≥ 1000
A4	≥ 1500
A5	≥ 2200
A6	≥ 3000
A7	≥ 4000
A8	≥ 5000
A9	> 6000

EUROPE

www.globusgroup.com

E: sales@globus.co.uk
T: +44 (0)161 877 4747
F: +44 (0)161 877 4746

MIDDLE EAST AND AFRICA

www.globusgroup.com/gcc

E: gcc@globusgroup.com
T: +971 4 882 9962
F: +971 4 882 9963

GLOBUS AMERICAS

www.globusgroup.com

E: americas@globusgroup.com



Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

©2023 Globus (Shetland) Ltd | SKY-DATA-TRC705-0623_1

EU compliance certificate delivered by the notified body INTERTEK ITALIA SPA, Via Guido Miglioli, 2/A - 20063 Cernusco sul Naviglio (MI) - Italia (Notified Body No. 2575)
UKCA compliance certificate delivered by the notified body ITS Testing Services UK Ltd, Centre Court, Meridian Business Park, Leicester, LE19 1WD, United Kingdom (Approved Body No. 0362)

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.