


LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	OWN
						APVD
			D2	REVISED PER ECO-11-010839	25MAY11	RK HMR

METRIC

DIMENSIONS LISTED IN mm [INCHES]


AMP WIRE RANGE	 E13288 Listed
26-22 AWG STRANDED	NOT LISTED
 LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

-  STAMP AMP APPROX AS SHOWN
-  CLEANED, UNPLATED



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
		WIRE CROSS SECTIONAL AREA RANGE: 0.1-0.41mm ² [202-810] CIR MILS STRANDED
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	
FOR ORDER ENTRY	1-800-526-5142	

-		31428-1
0.00254 [.000100] MIN TIN PER ASTM B-545		31428
FINISH		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 2-2-93	 TE Connectivity			
		CHK DA PATTERSON 2-2-93				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD DE MILLER 2-2-93	NAME			
			PRODUCT SPEC			
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± ± - FINISH		APPLICATION SPEC			
MATERIAL COPPER PER ASTM B-152 ANNEALED		WEIGHT -	SIZE A2			
		CUSTOMER DRAWING	CAGE CODE 00779		DRAWING NO G-31428	RESTRICTED TO -
			SCALE 10:1	SHEET 1 of 1	REV D2	