

DCV584L-QW

18V XR AC/DC L-Class Wet & Dry Vacuum

Selling Propositions

- Operates on 14.4V / 18V and 54V FLEXVOLT XR battery packs plus runs on a 240V mains supply
- On-board hose, cord and accessory storage provides convenient transport and storage
- High efficiency washable HEPA filter traps 99.97% of dust as fine as 0.3 Microns
- Versatile on the jobsite, vacuums wet or dry without the need to change the filter

Standard Equipment

- Wide nozzle (1)
- Batteries not included (1)
- 2 metre hose (1)
- Crevice tool (1)

Warranty specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Max. Airflow	15.9 l/sec
Tank Capacity	7.5 L
Wet/Dry	Yes
Wet/Dry Capacity	7.5 L
Hose length	2.0 m
Hose Connection	Air Lock
Hose Diameter	32.0 mm
Blower	Yes
Power Source	Cordless
Extraction Classification	L Class
Weight	4.5 kg
Weight (incl. battery)	5.14 kg
Length	430.0 mm
Width	305.0 mm
Height	330.0 mm
Sound Pressure	76.0 dB(A)
Sound Pressure Uncertainty	3.0 dB(A)
Sound Power	87.0 dB(A)
Sound Power Uncertainty	3.0 dB(A)