


PF0016/20/48 Datasheet

Product Name // IEC Connector Snap Fit To Panel Fused
Inlet 2 Pin PF0016 Series 2mm Panel Black 4.8mm Tab
Termination EN60 320-1 Standard Sheet C18 Class II

 [View Product Page](#)





List No.	DM A
PF0016/10/28	27.6
PF0016/10/48	27.6
PF0016/10/63	28.6

// **Product Description:**



Snap Fit Panel Mount Fused IEC Inlets



EN60 320-1 Standard Sheet C18 Class II



Cold Condition



Two Pin Class II (no Earth pin)



Single 5mm x 20mm fuse



Choice of panel thickness depending on part code: /10 - 1mm, /15 - 1.5mm, /20 - 2mm, /30 - 3mm



Choice of Termination depending on part code: /28 - 2.8mm Solder Tag, /48 - 4.8mm Tab, /63 - 6.3mm Tab



Choice of colour depending on part code: /WH - White, /GY - Grey, no suffix - Black (some approvals apply to specific colours only - see data for details)



Insulation Boot for rear of connector available separately (part code 11987)



Mate with PX0587, PX0587/SE, PX0588

// **General Information:**

Product Display Title:

Snap Fit Panel Mount Fused IEC Inlets

Product Family:

IEC Connectors

Product Series:

IEC60320 Main Inlets and Outlets

Approvals:

CSA, ENEC, UL, VDE, RCM

Body Material:

Nylon 66

Current Max:

10A

Flamability Rating:

UL94V-0

Function:

Panel Mount Fused Connector

Iec Connector Colour:

Black

Iec Connector Mates With:

PX0587,PX0587/SE,PX0588

Iec En60620 Type:

EN60 320-1 Standard Sheet C18 Class II

Max Operating Temperature:

+70°C

Min Operating Temperature:

-40°C

Max Panel Thickness:

2mm

Min Panel Thickness:

2mm

Number Of Contacts:

2 Contacts

Voltage Max:

250V

// **Product PDF Links**

 IEC Connectors product data

// **Product 3D CAD Model Links**

 PF0016/20/483D CAD Model