

Features

- The lockout device rotates freely around the valve hand wheel when locked, effectively preventing the valve from being turned.
- Made from strong Polyurethane plastic, providing resistance to cracking, abrasion, extreme weather, and temperature conditions.
- Gate valve lockout device has three padlock holes, allowing for secure locking with padlock.
- Accommodates rising stem valves, adding versatility for different types of valve systems.
- Compatible with hasps and padlocks, allowing multiple layers of security.
- Suitable for use in various industrial and maintenance settings where valve isolation is required.

RS PRO Gate Valve Lockout - Fits on Handle Wheel Dia From 165 To 254 mm (6³/₄" - 10" Inch)

RS Stock No.: 0710522



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Durable Polyurethane Construction – Built from tough polyurethane plastic that is resistant to cracking and abrasion, ensuring long-term, rugged performance in industrial environments.*
- *Rotating Locking Mechanism – Once applied and locked, the cover rotates freely around the valve handwheel, preventing unauthorized operation and keeping the valve securely locked.*
- *Padlock-Ready Design – Equipped with padlock holes, compatible with standard lockout hasps and padlocks, supporting single or multiple user lockouts.*
- *Versatile Application – The knockout center design allows accommodation of OS & Y (rising stem) valves, increasing compatibility with different valve types and installations.*
- *Secures Valve in Closed Position – Designed specifically to lock gate valves in the closed position, preventing accidental reactivation during maintenance or service.*
- *Enhanced Safety & Compliance – Provides an effective way to comply with LOTO (Lockout Tagout) protocols, enhancing workplace safety during mechanical isolation procedures.*

General Specifications

Type	Gate Valve Lockout
Material	Polyurethane Plastic
Colour	Red
Padlock holes	3
Package	LD + Corrugated box

Mechanical Specifications

Outside Dia (A)	266mm
Neck Dia (B)	89mm
Inside Dia (C)	254mm
Inside Depth (D)	52mm
Outside Depth (E)	63mm
Weight	510 Grams

Operation Environment Specifications

Withstand temperature	-20°C to 90°C.
-----------------------	----------------

